






APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	12/17/20	
A		UPDATE TITLE	6/25/21	WX/RC



RECOMMENDED PCB LAYOUT



SWITCH MARKINGS

CIRCUIT DIAGRAM
(SPDT) ON-ON



SPECIFICATIONS:

Material:

Movable contact: Copper Alloy, Silver plated

Terminals: Copper Alloy, Silver plated

Electrical:

Rating: 3 Amps with resistive load @ 125VAC or 28VDC

1.5 Amps with resistive load @ 250VAC

Contact resistance: 20 mohms max initial

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1500V RMS @ sea level

Electrical life: 30,000 make and break cycles at full load

Temperature Rating:

Operating temperature: -30°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	OW	12/17/20
CHECKED	AC	12/17/20
APPROVED		

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
SUB-MINIATURE ROCKER SWITCH, SPDT,
ON-ON, PCB RIGHT ANGLE TYPE

SIZE X	PART NO. SW-R3-2B-C-5-13	REV. A
REF: S00198T	SCALE: NTS	SHEET 1 OF 1