





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	12/3/04	
A		REDRAWN	7/02/09	
B		REVISED DIM.	5/30/11	
C		REVISED SPEC.	12/22/11	



RECOMMENDED PCB LAYOUT
(TOP VIEW)



Material:
Insulator: PBT, Glass filled, rated UL 94V-0
Insulator color: Black
Contacts: Brass
Shell: Brass, nickel plated
Plating:
Gold over Nickel underplate on contact area,
Tin over Copper underplate on PCB tails
Electrical:
Operating voltage: 30 VAC max.
Current rating: 1.5 Amp max @ 250V AC.
Contact resistance: 30 mohms max.
Insulation resistance: 1000 Mohms min.
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating:
Operating temperature: -20°C to +60°C
Environmental:
Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Railway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
.X	± .10	ØXX	± .10	TITLE UNIVERSAL SERIAL BUS SINGLE PORT, VERTICAL, PCB			
.XX	± .020	ØXX	± .015				
.XXX	± .015	ØXXX	± .010				
APPROVALS				DATE			
DRAWN	SS	10/4/04		SIZE	PART NO.	REV.	
CHECKED				X	USB-A-S-VT	C	
APPROVED				REF:	S0005C	SCALE:	NTS

SCALE: NTS

SHEET 1 OF 1