


# Data sheet

## chainflex® CF240.PUR



Data cable (Class 4.4.3.1) ● For medium duty applications ● PUR outer jacket ● Shielded ● Oil resistant and coolant-resistant ● Flame retardant ● PVC and halogen-free ● Notch-resistant ● Hydrolysis and microbe-resistant



1. Outer jacket: Pressure extruded PUR mixture
2. Overall shield: Extremely bending-resistant braiding made of tinned copper wires
3. Banding: Plastic foil
4. Core insulation: Mechanically high-quality TPE mixture
5. Conductor: Very finely stranded special cores of particularly high-flex design made of bare copper wires
6. Strain relief: Tensile stress-resistant centre element

**Example image**  
For detailed overview please see design table

### Cable structure

	<b>Conductor</b>	Very finely stranded special conductors of particularly bending resistant design made of bare copper wires.
	<b>Core insulation</b>	Mechanically high-quality TPE mixture.
	<b>Core structure</b>	The individual cores are wound in layers with a short pitch length.
	<b>Core identification</b>	Colour code in accordance with DIN 47100
	<b>Intermediate layer</b>	Foil taping over the outer layer.
	<b>Overall shield</b>	Extremely bending-resistant braiding made of tinned copper wires. Coverage approx. 70 % linear, approx. 90 % optical
	<b>Outer jacket</b>	Low-adhesion, halogen-free, highly abrasion resistant PUR mixture, adapted to suit the requirements in e-chains® (following DIN EN 50363-10-2). Colour: Window-grey (similar to RAL 7040) Printing: black

„00000 m“\* igus chainflex CF240.PUR.--① -----② E310776 cRUUs

AWM Style 20549 AWM I A/B 80°C 300V FT2 DNV TAE00003X3

CE RoHS-II conform www.igus.eu +++ chainflex cable works +++

\* **Length printing:** Not calibrated. Only intended as an orientation aid.  
① / ② Cable identification according to Part No. (see technical table).  
Example: ... chainflex **CF240.PUR.01.18 (18x0.14)C E310776** ...



igus 4-year  
chainflex cable  
guarantee and  
service life  
calculator based  
on 2 billion test  
cycles per year








# Data sheet

## chainflex® CF240.PUR



Data cable (Class 4.4.3.1) ● For medium duty applications ● PUR outer jacket ● Shielded  
● Oil resistant and coolant-resistant ● Flame retardant ● PVC and halogen-free ● Notch-resistant ● Hydrolysis and microbe-resistant

### Dynamic information

	<b>Bend radius</b>	<b>e-chain® linear</b> <b>flexible</b> <b>fixed</b>	minimum 10 x d minimum 8 x d minimum 5 x d
	<b>Temperature</b>	<b>e-chain® linear</b> <b>flexible</b> <b>fixed</b>	-25 °C up to +80 °C -40 °C up to +80 °C (following DIN EN 60811-504) -50 °C up to +80 °C (following DIN EN 50305)
	<b>v max.</b>	<b>unsupported</b> <b>gliding</b>	3 m/s 2 m/s
	<b>a max.</b>		20 m/s <sup>2</sup>
	<b>Travel distance</b>	Unsupported travels and up to 50 m for gliding applications, Class 4	



These values are based on specific applications or tests. They do not represent the limit of what is technically feasible.

### Guaranteed service life according to guarantee conditions

Double strokes	5 million		7.5 million		10 million	
Temperature, from/to [°C]	< 10 m	≥ 10 m	< 10 m	≥ 10 m	< 10 m	≥ 10 m
	R min. [x d]	R min. [x d]	R min. [x d]	R min. [x d]	R min. [x d]	R min. [x d]
-25/-15	12.5	15	13.5	16	14.5	17
-15/+70	10	12.5	11	13.5	12	14.5
+70/+80	12.5	15	13.5	16	14.5	17

Minimum guaranteed service life of the cable under the specified conditions.  
The installation of the cable is recommended within the middle temperature range.

### Electrical information

	<b>Nominal voltage</b>	300/300 V (following DIN VDE 0298-3) 300 V (following UL)
	<b>Testing voltage</b>	1500 V (following DIN EN 50395)



Example image

igus® chainflex® CF240.PUR

# Data sheet

## chainflex® CF240.PUR



Data cable (Class 4.4.3.1) ● For medium duty applications ● PUR outer jacket ● Shielded  
● Oil resistant and coolant-resistant ● Flame retardant ● PVC and halogen-free ● Notch-resistant ● Hydrolysis and microbe-resistant

### Properties and approvals

	UV resistance	Medium
	Oil resistance	Oil-resistant (following DIN EN 50363-10-2), Class 3
	Offshore	MUD-resistant following NEK 606 - status 2009
	Flame retardant	According to IEC 60332-1-2, FT2 / Horizontal Flame
	Silicone-free	Free from silicone which can affect paint adhesion (following PV 3.10.7 – status 1992)
	Halogen-free	Following DIN EN 60754
	PFAS-free	Use of PFAS-free materials according to the content of the REACH directive and its rules for the production and processing of chemical substances
	UL verified	Certificate No. V293560: „igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year“
	UL/CSA AWM	See data sheet for details ► <a href="http://www.igus.eu/CF240.PUR">www.igus.eu/CF240.PUR</a>
	NFPA	Following NFPA 79-2018, chapter 12.9
	DNV	Type approval certificate No. TAE00003X3
	REACH	In accordance with regulation (EC) No. 1907/2006 (REACH)
	Lead-free	Following 2011/65/EC (RoHS-II/RoHS-III)
	Cleanroom	According to ISO Class 1. The outer jacket material of this series complies with CF77. UL05.12.D - tested by IPA according to standard DIN EN ISO 14644-1
	CE	Following 2014/35/EU



igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year



### Properties and approvals

#### UL/CSA AWM Details

Conductor nominal cross section [mm²]	Number of cores	UL style core insulation	UL style outer jacket	UL Voltage Rating [V]	UL Temperature Rating [°C]
0.14	4-18	10493	20549	300	80
0.25	3-25	10493	20549	300	80
0.34	3-18	10493	20549	300	80

Example image

igus® chainflex® CF240.PUR

# Data sheet


## chainflex® CF240.PUR



Data cable (Class 4.4.3.1) ● For medium duty applications ● PUR outer jacket ● Shielded ● Oil resistant and coolant-resistant ● Flame retardant ● PVC and halogen-free ● Notch-resistant ● Hydrolysis and microbe-resistant

### Typical lab test setup for this cable series

Test bend radius R	approx. 50 - 115 mm
Test travel S	approx. 1 - 15 m
Test duration	minimum 2 - 4 million double strokes
Test speed	approx. 0.5 - 2 m / s
Test acceleration	approx. 0.5 - 1.5 m / s <sup>2</sup>



### Typical application areas

- For medium duty applications, Class 4
- Unsupported travel distances and up to 50 m for gliding applications, Class 4
- Almost unlimited resistance to oil, Class 3
- No torsion, Class 1
- Indoor and outdoor applications with average sun radiation
- Machining units/machine tools, Storage and retrieval units for high-bay warehouses, Packaging industry, quick handling, refrigerating sector



igus 4-year  
chainflex cable  
guarantee and  
service life  
calculator based  
on 2 billion test  
cycles per year



# Data sheet

## chainflex® CF240.PUR



Data cable (Class 4.4.3.1) ● For medium duty applications ● PUR outer jacket ● Shielded  
● Oil resistant and coolant-resistant ● Flame retardant ● PVC and halogen-free ● Notch-resistant ● Hydrolysis and microbe-resistant

### Technical tables:

#### Mechanical information

Part No.	Number of cores and conductor nominal cross section [mm²]	Outer diameter (d) max. [mm]	Copper index [kg/km]	Weight [kg/km]
CF240.PUR.01.04	(4x0.14)C	5.5	15	39
CF240.PUR.01.07	(7x0.14)C	6.5	24	54
CF240.PUR.01.08	(8x0.14)C	7.0	26	64
CF240.PUR.01.14	(14x0.14)C	7.5	41	79
CF240.PUR.01.18	(18x0.14)C	8.0	51	97
CF240.PUR.01.25	(25x0.14)C	8.5	66	101
CF240.PUR.02.03	(3x0.25)C	5.5	18	41
CF240.PUR.02.04	(4x0.25)C	6.0	22	45
CF240.PUR.02.05	(5x0.25)C	6.0	25	50
CF240.PUR.02.07	(7x0.25)C	7.0	33	65
CF240.PUR.02.08	(8x0.25)C	7.0	39	72
CF240.PUR.02.14	(14x0.25)C	8.0	60	103
CF240.PUR.02.18	(18x0.25)C	9.0	71	122
CF240.PUR.02.25	(25x0.25)C	10.5	97	152
CF240.PUR.03.03	(3x0.34)C	5.0	25	47
CF240.PUR.03.04	(4x0.34)C	5.5	30	54
CF240.PUR.03.05	(5x0.34)C	6.0	34	60
CF240.PUR.03.07	(7x0.34)C	6.5	45	84
CF240.PUR.03.14	(14x0.34)C	8.0	74	126
CF240.PUR.03.18	(18x0.34)C	8.5	91	156

**Note:** The given outer diameters are maximum values and may tend toward lower tolerance limits.

G = with green-yellow earth core x = without earth core

#### Electrical information

Conductor nominal cross section [mm²]	Maximum conductor resistance at 20 °C (following DIN EN 50289-1-2) [Ω/km]	Max. current rating at 30 °C [A]
0.14	138	2.5
0.25	79	5
0.34	57	7

The final maximum current rating depends among other things on the ambient conditions, the type of the installation and the number of loaded cores.



igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year



Example image

igus® chainflex® CF240.PUR

# Data sheet

## chainflex® CF240.PUR



Data cable (Class 4.4.3.1) ● For medium duty applications ● PUR outer jacket ● Shielded  
● Oil resistant and coolant-resistant ● Flame retardant ● PVC and halogen-free ● Notch-resistant ● Hydrolysis and microbe-resistant

### Design table

Part No.	Number of cores	Core design	Part No.	Number of cores	Core design
CF240.PUR.XX.03	3		CF240.PUR.XX.08	8	
CF240.PUR.XX.04	4		CF240.PUR.XX.14	14	
CF240.PUR.XX.05	5		CF240.PUR.XX.18	18	
CF240.PUR.XX.07	7		CF240.PUR.XX.25	25	



igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year



Example image

# Data sheet

## chainflex® CF240.PUR



Data cable (Class 4.4.3.1) ● For medium duty applications ● PUR outer jacket ● Shielded  
● Oil resistant and coolant-resistant ● Flame retardant ● PVC and halogen-free ● Notch-resistant ● Hydrolysis and microbe-resistant



### Colour code in accordance with DIN 47100

Conductor no.	Colours according to DIN ISO 47100	Conductor no.	Colours according to DIN ISO 47100
1	white	19	white-pink
2	brown	20	pink-brown
3	green	21	white-blue
4	yellow	22	brown-blue
5	grey	23	white-red
6	pink	24	brown-red
7	blue	25	white-black
8	red	26	brown-black
9	black	27	grey-green
10	violet	28	yellow-grey
11	grey-pink	29	pink-green
12	red-blue	30	yellow-pink
13	white-green	31	green-blue
14	brown-green	32	yellow-blue
15	white-yellow	33	green-red
16	yellow-brown	34	yellow-red
17	white-grey	35	green-black
18	grey-brown	36	yellow-black



igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year

