



Representative Image

Alternate Catalog No. S803S-K20 Catalog No. 2CCS863001R0487

Description: MCB S800S 3P K 20A

UPC No 7612271201715

Home > Circuit Breakers > Miniature Circuit Breakers > Supplementary Protectors

The S803S-K20 is a 3-pole High Performance Circuit breaker with K-Characteristic, with cage terminal and a rated current of 20 A. It is a current limiting device with a maximum breaking capacity of 50kA at 240/415V. It can be used for voltages up to 400/690V and in DC as well. It has two different tripping mechanisms, the thermal tripping mechanism for overload protection and the electromechanic tripping mechanism for short circuit protection. The S803S-K20 complies with IEC/EN 60898-1 and IEC/EN 60947-2 and allows the use for residential, commercial and industrial applications. It has numerous of approvals, therefore it can be used worldwide. The extensive range of accessory makes the use of S803S-K20 more comfortable. Due to the fast arc extinction of S803S-K20 your application will be secured.

Descriptors

| | |
|----------|--------------------------|
| Category | Supplementary Protectors |
|----------|--------------------------|

Specifications

| | |
|--|---|
| Number of Poles | 3 |
| Tripping Characteristic | K |
| Rated Current | 20 A |
| Standards | IEC/EN 60947-2 UL 1077 |
| Product Main Type | S800S |
| Rated Voltage (V) | (240 V AC) (480Y / 277 V AC) (600Y / 347 V AC) |
| Interrupting Rating acc. to UL1077 | (240 V AC) 30 kA (480Y / 277 V AC) 14 kA (600Y / 347 V AC) 6 kA |
| Rated Ultimate Short-Circuit Breaking Capacity | (240 / 415 V AC) 50 kA (254 / 440 V AC) 30 kA (400 / 690 V AC) 6 kA (125 V DC) 30 kA |
| Power Loss | at Rated Operating Conditions per Pole 4.3 W |