

TRB Plug Full Crimp Connector for TRC-50-2 Cable

LCCN310-06031-310



Configuration

- TRB Plug Connector
- Straight Body Geometry
- TRC-50-2, M17/134-00002 Interface Type
- Crimp/Solder Attachment

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		500	MHz
Operating Voltage (AC)			5,000	Vrms

Mechanical Specifications

Size

Length	1.34 in [34.04 mm]
Width	0.50 in [12.70 mm]
Height	0.50 in [12.70 mm]
Weight	0.05 lbs [22.68 g]
Mating Cycles	500 Cycles

Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold
Insulation	PTFE	
Body	Brass	Nickel
Coupling Nut	Brass	Nickel
Washer	Brass	Nickel
Shrink Tubing	PVDF	

Environmental Specifications

Temperature

Operating Range	-65deg C to +165deg C
-----------------	-----------------------

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[TRB Plug Full Crimp Connector for TRC-50-2 Cable LCCN310-06031-310](#)

TRB Plug Full Crimp Connector for TRC-50-2 Cable

LCCN310-06031-310



Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

TRB Plug Full Crimp Connector for TRC-50-2 Cable from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: TRB Plug Full Crimp Connector for TRC-50-2 Cable LCCN310-06031-310

URL: <https://www.l-com.com/trb-plug-full-crimp-connector-trc-50-2-cable-lccn310-06031-310-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

