



Alternate Catalog No. AF80-22-00-11 Catalog No. 1SBL397501R1100

Description: AF80-22-00-11 24-60V50/60HZ 20-60VDC Contactor

UPC No 3471523133914

Home > Contactors & Starters > UL Listed IEC Contactors > AF Contactors

AF80 4-pole contactors are used for controlling power circuits up to 690 V AC and 440 V DC. They are mainly used for controlling non-inductive or slightly inductive loads (i.e. resistance furnaces...). AF... contactors include an electronic coil interface accepting a wide control voltage Uc min. ... Uc max. Only four coils cover control voltages between 24...500 V 50/60 Hz or 20...500 V DC. AF contactors can manage large control voltage variations. One coil can be used for different control voltages used worldwide without any coil change. AF contactors have built-in surge protection and do not require additional surge suppressors. The AF... series 4-pole contactors are of the block type design. - Main poles and auxiliary contact blocks: 2 N.O. + 2 N.C. main poles, front and side-mounted add-on auxiliary contact blocks (mechanically-linked auxiliary contacts compliant with Annex L of IEC 60947-5-1. N.C. mirror contacts compliant with Annex F of IEC 60947-4-1) - Control circuit: AC or DC operated - Accessories: a wide range of accessories is available.

Descriptors	
Category	AF Contactors
Block Contactor Type	4-Pole Contactor

Specifications	
Product Type	AF
General Use Rating UL/CSA	(600 V AC) 105 A
Object Classification Code	Q
Terminal Type	Screw Terminals
Rated Control Circuit Voltage	50 Hz /60 Hz 24 60 V DC Operation 20 60 V
Number of Main Contacts NO	2
Number of Main Contacts NC	2
Climatic Withstand	Category B according to IEC 60947-1 Annex Q
Resistance to Vibrations acc. to IEC 60068-2-6	5 300 Hz 3 g Closed position / 2 g Open position
Number of Auxiliary Contacts NO	0
RoHS Status	Following EU Directive 2011/65/EU
Reference Ambient Air Temperature	Close to Contactor for Storage -60 +80 °C Near Contactor for Operation in Free Air -40 +70 °C
Rated Operational Voltage	Main Circuit 690 V
Number of Auxiliary Contacts NC	0
Maximum Operating Altitude Permissible	3000 m
Rated Operational Current AC-1	(690 V) 40 °C 125 A (690 V) 60 °C 105 A (690 V) 70 °C 90 A
Rated Operational Power AC-3	(220 / 230 / 240 V) 22 KWT (380 / 400 V) 37 KWT (415 V) 45 KWT (440 V) 45 KWT (500 V) 45 KWT (690 V) 45 KWT
Horsepower Rating UL/CSA	(220 240 V AC) Three Phase 30 hp (440 480 V AC) Three Phase 60 hp (550 600 V AC) Three Phase 75 hp (120 V AC) Single Phase 7-1/2 hp (200 208 V AC) Three Phase 25 hp (240 V AC) Single Phase 15 hp

Specifications	
Conventional Free-air Thermal Current	acc. to IEC 60947-4-1, Open Contactors $q = 40 ^{\circ}\text{C}$ 125 A
Rated Frequency	Main Circuit 50Hz Main Circuit 60 Hz
Rated Short-time Withstand Current	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 780 A at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 140 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 300 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 1200 A at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 450 A for 1 s - A
Rated Operational Current AC-3	(220 / 230 / 240 V) 60 °C 80 A (380 / 400 V) 60 °C 80 A (415 V) 60 °C 80 A (440 V) 60 °C 80 A (500 V) 60 °C 65 A (690 V) 60 °C 49 A
Maximum Electrical Switching Frequency	AC-1 600 cycles per hour
Rated Insulation Voltage	acc. to UL/CSA 600 V acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 1000 V
Maximum Mechanical Switching Frequency	3600 cycles per hour
Secondary Rated Impulse Withstand Voltage	8 kV
Connecting Capacity Main Circuit	Rigid 1x 6 70 m²/2x 6 50 m² / Flexible with Ferrule 1/2x 6 50 m²
Connecting Capacity Control Circuit	Flexible with Ferrule 1/2x 0.75 2.5 m ² Rigid 1/2x 1 2.5 m ²
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP10
Screw Terminal Type	Screw Terminals
Wire Stripping Length	Main Circuit 17 mm
Classifications	
ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 6.0	EC000066 - Power contactor, AC switching
ETIM 7	EC000066 - Power contactor, AC switching
ETIM 5.0	EC000066 - Magnet contactor, AC-switching

125.5 mm		
Package Information		
150 mm		
103 mm		
150 mm		
3471523133914		
box 1 piece		
250 mm		
300 mm		
1.62 kg		
box 8 piece		
192 piece		
300 mm		

1.49 kg

116 mm

90 mm

electrification.us.abb.com Created on: 03/22/2024

Product Net Weight

Product Net Width

Product Net Depth / Length

Package Information	
Package Level 2 Gross Weight	12.96 kg
Ordering	
Minimum Order Quantity	1
Customs Tariff Number	85364900

electrification.us.abb.com Created on: 03/22/2024