

Low Loss Ultra Flexible LMR-600-UF Indoor Outdoor Rated Coax Cable Double Shielded with Black TPE Jacket



LMR-600-UF-LC-BULK

Times Microwave Systems Coax Cable Specification

Configuration

- · Low Loss, Outdoor Flexible Cable
- 2 Shield(s)

Features

- · TPE Jacket
- Max Operating Temperature +85°C
- · Min Install Bend Radius of 1.5 inches

Applications

- · RF Test Systems
- · Antenna Installations

- · Phase Velocity 87% VoP
- · Max Operating Frequency of 8 GHz
- Ultra Flexible Coax
- · Laboratory Applications
- · General Purpose RF Interconnect

Description

LMR-600-UF-LC-BULK coax cable from L-com is only one of a large number of radio frequency coaxial cable types specifically stocked to be ready for quick shipment. L-com LMR-600-UF-LC-BULK coax cable is manufactured in a flexible design and has a 50 Ohm impedance. This low loss flexible 50 Ohm coax cable LMR-600-UF-LC-BULK is constructed with a 0.590 inch diameter and Black TPE jacket.

LMR-600-UF-LC-BULK flexible 50 Ohm coax cable with PVC jacket is rated for a 8 GHz maximum operating frequency. This 50 Ohm 0.590 inch diameter and low loss flexible coax cable is built with a double shield count and RF shielding of 90 dB. L-com LMR-600-UF-LC-BULK coax is constructed with Foam PE dielectric and a maximum operating temperature of +85 degrees C. Times Microwave LMR-600-UF-LC-BULK coax cable specs for this wire properties can be found on its RF coax cable LMR-600-UF-LC-BULK datasheet.

LMR-600-UF-LC-BULK cable is part of more than one million RF, microwave parts in stock at L-com. This Times Microwave low loss LMR-600-UF-LC-BULK coax cable is ready to buy and can be shipped worldwide. L-com also maintains a wide selection of other radio frequency coaxial cable types that ship same-day from our warehouse as with the rest of our other RF/microwave components.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|--------------------------------------|---------|--------------|---------|--------------|
| Frequency Range | DC | | 8 | GHz |
| Impedance | | 50 | | Ohms |
| Velocity of Propagation | | 87 | | % |
| Time Delay | | 1.17 [3.84] | | ns/ft [ns/m] |
| Shielding Effectiveness | 90 | | | dB |
| Dielectric Withstanding Voltage (DC) | | | 4,000 | Vdc |
| Jacket Spark | | | 8,000 | Vrms |
| Inner Conductor DC Resistance | | | 0.43 | Ohms/1000ft |
| Outer Conductor DC Resistance | | | 1.2 | Ohms/1000ft |
| Nominal Capacitance | | 23.4 [76.77] | | pF/ft [pF/m] |
| Nominal Inductance | | 0.058 [0.19] | | uH/ft [uH/m] |

^{*} LMR™ is a trademark of Times Microwave Systems.



Low Loss Ultra Flexible LMR-600-UF Indoor Outdoor Rated Coax Cable Double Shielded with Black TPE Jacket



LMR-600-UF-LC-BULK

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|--------------------|---------|---------|---------|--------|
| Input Power (Peak) | | | 40 | kWatts |

Performance by Frequency Band

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------------|-------|-------|-------|-------|------|----------|
| Frequency | 50 | 150 | 220 | 450 | 900 | MHz |
| Attenuation, Typ | 0.7 | 1.2 | 1.4 | 2.1 | 3 | dB/100ft |
| | 2.3 | 3.94 | 4.59 | 6.89 | 9.84 | dB/100m |
| Input Power (CW), Max | 3,530 | 2,000 | 1,640 | 1,120 | 770 | Watts |

| Description | F6 | F7 | F8 | F9 | F10 | Units |
|-----------------------|-------|-------|-------|-------|-------|----------|
| Frequency | 1.5 | 1.8 | 2 | 2.5 | 5.8 | GHz |
| Attenuation, Typ | 4 | 4.4 | 4.7 | 5.3 | 8.7 | dB/100ft |
| | 13.12 | 14.44 | 15.42 | 17.39 | 28.54 | dB/100m |
| Input Power (CW), Max | 580 | 520 | 490 | 430 | 260 | Watts |

Mechanical Specifications

Diameter Weight

Min. Bend Radius (Installation) Min. Bend Radius (Repeated)

Bending Moment Tensile Strength Flat Plate Crush 0.59 in [14.99 mm] 0.165 lbs/ft [0.25 kg/m] 1.5 in [38.1 mm] 6 in [152.4 mm] 1.75 lbs-ft [2.37 N-m] 350 lbs [158.76 kg]

40 lbs/in [0.71 kg/mm]

Construction Specifications

| Description | Material and Plating | Diameter |
|-----------------|----------------------|---------------------|
| Inner Conductor | Copper, 1 Strand | 0.176 in [4.47 mm] |
| Conductor Type | Stranded | |
| Dielectric | Foam PE | 0.455 in [11.56 mm] |
| First Shield | Aluminum Tape | |
| Second Shield | Tinned Copper | |
| Jacket | TPE, Black | 0.59 in [14.99 mm] |

Environmental Specifications

Temperature

Operating Range -40 to +85 deg C Installation Range -40 to +85 deg C Storage Range -70 to +85 deg C



Low Loss Ultra Flexible LMR-600-UF Indoor Outdoor Rated Coax Cable Double Shielded with Black TPE Jacket



LMR-600-UF-LC-BULK

Environmental Specification Notes: Indoor/Outdoor

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Low Loss Ultra Flexible LMR-600-UF Indoor Outdoor Rated Coax Cable Double Shielded with Black TPE Jacket from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: https://www.l-com.com/low-loss-ultra-flexible-Imr-600-uf-indoor-outdoor-rated-coax-cable-double-shielded-black-tpe-jacket-by-the-foot-Imr-600-uf-lc-bulk-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

LMR-600-UF-LC-BULK CAD Drawing

Low Loss Ultra Flexible LMR-600-UF Indoor Outdoor Rated Coax Cable Double Shielded with Black TPE Jacket

