

Low power submersible liquid level transmitter, 10 m range, RS485, direct lead, 10 m cable

# LTSUB7002-3204 Liquid Level Sensors

#### **Features**

- · Suitable for low power applications
- · Excellent shock and vibration resistance
- · High precision and long term stable performance
- · Corrosion resistant stainless steel housing
- · RS-485 output

### **Applications**

- · Petroleum Industry
- · Water and Sewage Treatment
- · Chemical Production

- · Food and Beverage
- · Hydrostatic level monitoring

## **Description**

The LTSUB7002-3204 Submersible liquid level transmitter is specifically designed for monitoring hydrostatic pressure. This pressure is then converted to a signal that corresponds to the height of the liquid above it. Being a compact device allows it to be used in applications where space is limited. It is easy to install and provides accurate, reliable measurements regardless of the shape or size of the tanks used in industrial processes and other industrial automation applications where liquid level monitoring is needed.

#### **General Specifications**

Application: Level Sensing
Sensor Type: Submersible
Electrical Connection: Direct Lead

Connection Type: 10 meter 4 wire cable

Output Signal: RS-485

Interface Protocol: MODBUS-RTU

Media Compatibility: Water/Gasoline/Other fluids

Description	Minimum	Typical	Maximum	Unit
Sensing Distance			10,000	mm
Accuracy		0.5		% Full Scale
Overpressure		200		xFull Scale
Long-Term Stability			0.2	% Full Scale/year

#### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Unit	
DC Power Supply Voltage	3		4.2	VDC	
Power Supply Current			2.5	mA	

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Low power submersible liquid level transmitter, 10 m range, RS485, direct lead, 10 m cable LTSUB7002-3204



Low power submersible liquid level transmitter, 10 m range, RS485, direct lead, 10 m cable

# LTSUB7002-3204 Liquid Level Sensors

Stand-by Current 0.2 mA

## **Material Specifications**

Description	Material	
Cable Material	PVC	
Housing Material	Stainless steel	

### **Environmental Specifications**

Temperature (Operating) -10 deg C to 85 deg C

Temperature (Storage) -20 deg C to 100 deg C

Temperature (Compensated) -10 deg C to 70 deg C

Ingress Protection IP68

Notes: Media cannot be frozen

The Infinite Electronics portfolio includes coaxial cable assemblies, connectors, adapters and custom products, as well as our wireless product line which includes antennas, RF amplifiers, lightning and surge protectors, and NEMA rated enclosures.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume any liability arising out of the use of any part or documentation.

LTSUB7002-3204 CAD Drawing
Low power submersible liquid level transmitter, 10 m range, RS485, direct lead, 10 m cable

