



Representative Image

Alternate Catalog No. B6-22-00-80

Catalog No. GJL1211501R8000

Description: B6-22-00-80 Mini Contactor 220-240V 40-450Hz

UPC No 4013614152627

[Home](#) > [Contactors & Starters](#) > [UL Listed IEC Contactors](#) > [AF Contactors](#)

The B6-22-00 mini contactor is a compact 4 pole contactor with screw terminals. They are ideally suited for applications where reliability is a must and space is at a premium. Mini contactors are used in residential buildings, commercial buildings and industrial applications for the control of single or three-phase loads up to 4 kW (AC-3) and 20 A / 690 V (AC-1) or switching of control signals. Further features are the silent coil, a switch position indication and the integrated possibility for rail or wall mounting.

Descriptors

Category

AF Contactors

Specifications

Product Type	Mini Contactors (B6, B7)
General Use Rating UL/CSA	(300 V AC) 12 A
Object Classification Code	Q
Terminal Type	Screw Terminals
Rated Control Circuit Voltage	220 ... 240 V AC
Number of Main Contacts NO	2
Connecting Capacity Auxiliary Circuit UL/CSA	Stranded 1/2x 22-10 american wire gauge
Number of Main Contacts NC	2
Maximum Operating Voltage UL/CSA	Main Circuit 600 V AC Auxiliary Circuit 600 V AC / DC
Connecting Capacity Main Circuit UL/CSA	Stranded 1/2x 22-10 american wire gauge
Resistance to Vibrations acc. to IEC 60068-2-6	5g / 5 ... 150 Hz
Number of Auxiliary Contacts NO	0
Connecting Capacity Main Circuit UL/CSA	Stranded 1/2x 22-10 american wire gauge
RoHS Status	Following EU Directive 2011/65/EU
Reference Ambient Air Temperature	Operation -20 ... +55 °C
Rated Operational Voltage	Main Circuit 12 ... 690 V AC / DC Main Circuit 690 V AC
Resistance to Shock acc. to IEC 60068-2-27	11 ms Pulse 15g
Number of Auxiliary Contacts NC	0
Tightening Torque UL/CSA	Auxiliary Circuit 7 in-lb (pound inch) Control Circuit 7 in-lb (pound inch) Main Circuit 7 in-lb (pound inch)
Maximum Operating Altitude Permissible	2000 m
Rated Operational Current AC-1	(220 / 240 V) 40 °C 20 A (220 / 240 V) 55 °C 16 A (380 / 440 V) 40 °C 20 A (380 / 440 V) 55 °C 16 A (690 V) 40 °C 6 A (690 V) 55 °C 6 A
Standards	IEC/EN 60947-1 IEC/EN 60947-4-1 IEC/EN 60947-5-1 UL 60947-1 UL 60947-4-1

by ABB

Specifications

Rated Operational Power AC-3	(220 / 230 / 240 V) 2.2 kW (400 V) 4 kW (400 V) Three Phase 4 kW (440 V) 4 kW (500 V) 4 kW (690 V) 3 kW
Rated Breaking Capacity AC-3 acc. to IEC 60947-4-1	8 x I _e / AC-3
Horsepower Rating UL/CSA	(208 V AC) Three Phase 1 hp (220 ... 240 V AC) Single Phase 0.5 hp (220 ... 240 V AC) Three Phase 2 hp (440 ... 480 V AC) Three Phase 3 hp (550 ... 600 V AC) Three Phase 1 hp
Conventional Free-air Thermal Current	Main Circuit 20 A
Rated Frequency	Control Circuit 400 Hz Control Circuit 50 Hz Control Circuit 60 Hz Main Circuit 60 Hz Main Circuit 50Hz Main Circuit DC
Rated Short-time Withstand Current	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 64 A
Rated Operational Current AC-3	(220 / 230 / 240 V) 55 °C 8.5 A (380 / 400 V) 55 °C 8.5 A (440 V) 55 °C 7.4 A (500 V) 55 °C 6.8 A (690 V) 55 °C 3.8 A
Rated Making Capacity AC-3 acc. to IEC 60947-4-1	10 x I _e / AC-3
Maximum Electrical Switching Frequency	AC-1 300 cycles per hour AC-15 360 cycles per hour AC-3 600 cycles per hour DC-1 600 cycles per hour DC-13 360 cycles per hour DC-3 600 cycles per hour
Short-Circuit Protective Devices	gG Type Fuses Type 1 25 A
Rated Insulation Voltage	690 V acc. to UL/CSA 600 V
Mechanical Durability	10000000 cycle
Coil Operating Limits	(acc. to IEC 60947-4-1) for AC supply 0.85 ... 1.1 x U _c (at θ ≤ 55 °C)
Secondary Rated Impulse Withstand Voltage	Auxiliary Circuit 6 kV Main Circuit 6 kV
Connecting Capacity Main Circuit	Flexible with Ferrule 1/2x 1 ... 2.5 square mm Flexible with Insulated Ferrule 1/2x 1 ... 2.5 square mm Flexible 1/2x 1 ... 2.5 square mm Rigid 1/2x 1 ... 4 square mm
Connecting Capacity Control Circuit	Flexible with Ferrule 1/2x 1 ... 2.5 square mm Flexible with Insulated Ferrule 1/2x 1 ... 2.5 square mm Flexible 1/2x 1 ... 2.5 square mm Rigid 1/2x 1 ... 4 square mm
Coil Consumption	Average Holding Value 50 Hz 3.5 V - A Average Pull-in Value 50 Hz 3.5 V - A
Degree of Protection	Auxiliary Circuit Terminals IP20 Control Circuit Terminals IP20 Main Circuit Terminals IP20
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 1/2x 1 ... 2.5 square millimetre Flexible with Insulated Ferrule 1/2x 1 ... 2.5 square millimetre Flexible 1/2x 1 ... 2.5 square millimetre Rigid 1/2x 1 ... 4 square millimetre
Mounting on DIN Rail	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Screw Terminal Type	Screw Terminals
Wire Stripping Length	Auxiliary Circuit 9 mm Main Circuit 9 mm

Classifications

ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 6.0	EC000066 - Power contactor, AC switching
ETIM 7	EC000066 - Power contactor, AC switching

Classifications

ETIM 5.0	EC000066 - Magnet contactor, AC-switching
eClass	7.0 27371003

Dimensions

Product Net Weight	0.175 kg
Product Net Depth / Length	46.5 mm
Product Net Width	52.5 mm
Product Net Height	57.5 mm

Package Information

Package Level 1 Width	115 mm
Package Level 1 Height	54 mm
Package Level 1 Depth / Length	280 mm
Package Level 1 EAN	4013614413483
Package Level 1 Units	10 piece
Package Level 1 Gross Weight	1.82 kg

Ordering

Minimum Order Quantity	1
Customs Tariff Number	85365080