

WL Series Liquid Cooling System

The WL2000 is a re-circulating liquid to air heat exchanger that offers dependable, compact performance by removing large amounts of heat from a liquid circuit. The coolant is re-circulated using a high pressure pump to assure maximum flow rate. Heat from coolant is absorbed by a radiant heat exchanger and dissipated into the ambient environment using brand name fan. Manual adjustments can be made to control flow switch. Customized features are available, however, MOQ applies.




Features

- Cooling to ambient
- High heat pumping capacity
- Compact form factor
- Long life operation

Applications

- Cooling Particle Accelerators: Linear Accelerators and Cyclotrons
- Semiconductor Fabrication Equipment Cooling
- X-ray Cooling in Industrial Scanners



Fluid Operating Points

100% Water

Cooling Power (Q_c) = 2000 Watts
Thermal Conductance = 181.0 W/°C
 ΔT (Ambient-Coolant)* = 11.0 °C
 ΔT (Outlet-Inlet)** @ 4.4 L/min = 6.5 °C

60/40 Water-Glycol

Cooling Power (Q_c) = 2000 Watts
Thermal Conductance = 153.8 W/°C
 ΔT (Ambient-Coolant)* = 13.0 °C
 ΔT (Outlet-Inlet)** @ 4.4 L/min = 7.1 °C

70/30 Water-Glycol

Cooling Power (Q_c) = 2000 Watts
Thermal Conductance = 160.2 W/°C
 ΔT (Ambient-Coolant)* = 12.5 °C
 ΔT (Outlet-Inlet)** @ 4.4 L/min = 6.9 °C


50/50 Water-Glycol

Cooling Power (Q_c) = 2000 Watts
Thermal Conductance = 148.1 W/°C
 ΔT (Ambient-Coolant)* = 13.5 °C
 ΔT (Outlet-Inlet)** @ 4.4 L/min = 7.5 °C


* ΔT (Ambient-Coolant) is the temperature difference between the ambient temperature and the coolant temperature that is at the outlet of the heat exchanger during steady-state operation. This temperature difference would initially be 0 and increase to the steady state value under load. This would also be the temperature at the inlet to the application.

** ΔT (Outlet-Inlet) is the temperature difference between the inlet temperature and the outlet temperature of the application at the nominal coolant flow. More flow (application pressure drop less than nominal) would necessarily mean a smaller ΔT .


WL2000 Heat Dissipation
2000 Watt Requirement



WL2000 Fluid Inlet/Outlet Temperature Differ
@ Nominal Flow 4.4 L/min



WL2000 - Pump Curve



Technical Specifications

Performance

Nominal Cooling Capacity	2,000 W
Nominal Operating Flowrate (60 Hz)	4.4 L/min @ 5.5 Bar
Nominal Operating Flowrate (50 Hz)	4.4 L/min @ 5.1 Bar

Operation

Coolant	Water or Water/Glycol
Operating Temperature	10°C to 40°C
Storage temperature range (w/o coolant)	-25°C to 70°C
Humidity range	20% to 80%
Storage Humidity range	5% to 95%, non-condensing
Input Voltage	230 VAC
Frequency	50/60 Hz
Current	< 2.1 Amps
Noise	< 70 dB(A)
Flow Switch Open	≤ 4 L/min
Input Power Connection	Terminal Block
Maximum Forward Pressure	6 Bar

Physical

Height	505 mm
Length	300 mm
Width	305 mm
Weight	26.5 kg
Coolant Capacity	2.5 Liters
Couplings	Walther Type MD 006

Features	Applications
Compact design	Medical imaging systems
Reliable operation	Photonics laser systems
Adjustable flow switch	X-Ray scanning systems
Bypass valve protection	Semiconductor fabrication

Notes

Check coolant level regularly. For optimal cooling performance, coolant level should always be above radiator fins.
Hose selection should be of material and thickness to support pressure resistance and coolant type.
Manual adjustments can be made to control pressure and flow rate.
Check pump filter and dust on heat exchanger periodically for cleaning.

Any information furnished by Tark Thermal Solutions and its agents, whether in specifications, data sheets, product catalogues or otherwise, is believed to be (but is not warranted as being) accurate and reliable, is provided for information only and does not form part of any contract with Tark Thermal Solutions. All specifications are subject to change without notice. Tark Thermal Solutions assumes no responsibility and disclaims all liability for losses or damages resulting from use of or reliance on this information. All Tark products are sold subject to the Tark Thermal Solutions Terms and Conditions of sale (including Tark’s limited warranty) in effect from time to time, a copy of which will be furnished upon request.

© Copyright 2025 Tark Thermal Solutions, Inc. All rights reserved.

Revision: 01 Date: 06-29-2025

Print Date: 06-29-2025