






Outer shell	: Brass (UNS C38500)	Chrome plated (SAE AMS 2460)
Earthing crown	: Bronze (UNS C54400)	Nickel plated (SAE AMS QQ N 290)
Insulator	: LCP A130	-
Conical nut	: Brass (UNS C38500)	Chrome plated (SAE AMS 2460)
Locking washer	: Bronze (UNS C52100)	Nickel plated (SAE AMS QQ N 290)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (SAE AMS QQ N 290)

Panel cut-out



Torque for
mounting
nut : 9 Nm

**Fixed socket , with two nuts , with keys (K) ,
with extended insulator . (Back panel mounting) .
Series 3B , multipole (26) (without contacts)**

ETUDE N° E1308-E1243-E4255

Echelle —	Dessiné	13.07.2020	OVU / JPBA
	Contrôle	13.07.2020	NHA / CDE
	Modif.	00	13.07.2020/ OVU



LEMO

LEMO SA
Chemin des Champs-Courbes 28
1024 Ecublens - SWITZERLAND

Tel. (+41 21) 695 16 00
email : info@lemo.com
www.lemo.com

ECK.3B.326.CBZ