



Image for illustrative purpose only

Summary

Request a quote	
Catalog	
Number of contacts Low Voltage	6
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Size	1S
Suggested matching part	FFA.1S.306.CLAC42
Series	S - Indoor Stepped Insert

Technical details

Electrical Configuration

Number of contacts Low Voltage	6
Contact Termination Low voltage	PCB - Elbow
Insert configuration value	1S.306 - 6 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Test voltage (kV DC)	1.7
Contact Dia.	0.7

Form & Material

Shell style / Model id	ECP - Fixed receptacle with two nuts, long threaded shell, with elbow contacts for printed circuit (back panel mounting)
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Hermaphroditic keying (half moon insert) with female pin 1
Colour	Grey
Weight	11.57 g


Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ecp-1s-306-clv.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Drawings



Dimensions

	E	M	e	A	B	S3	N	S1
mm.	10	3.5	M12x1.0	16	16	14	17.5	10.5
in.	0.39	0.14		0.63	0.63	0.55	0.69	0.41

Recommended By Lemo

Accessories

Compatible cap	BRE.1S.200.NAS
----------------	--------------------------------