

LCCA31068-FT3

Configuration

Connector 1: 4.3-10 MaleConnector 2: 7/16 DIN MaleCable Type: TFT-5G-402

Features

- 100% Tested with PIM Test Results Marked on Cable
- · Lightweight and Extremely Flexible
- · Low Loss with Excellent VSWR

Applications

- · Distributed Antenna Systems (DAS)
- · Plenum Installations

- IP67 (when mated)
- · Using Times Microwave Components
- Multi-Carrier Communication Systems
- · PIM Testing



Description

L-com's LCCA31068-FT3 is a 4.3-10 male to 7/16 DIN male low PIM cable using TFT-402-LF coax using Times Microwave components 3 foot and ships same-day. The TFT-5G-402 coax of this 4.3-10 cable uses the PTFE dielectric with a VoP of 76%. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com 4.3-10 to 7/16 DIN cable assembly has a male to male gender configuration with flexible TFT-5G-402 series coax and operates to 5.8 GHz. The double shield of this 4.3-10 cable is layered by over providing shielding effectiveness greater than 80dB. With passive intermodulation levels better than -160 dBc, our cable assembly design is ideal where low PIM is desired. Times Microwave cable is used in each assembly and TMS components are used to form connections with the super flexible low PIM cable. These cable assemblies are expertly built to satisfy your specific need with high quality Times Microwave Systems manufactured parts.

Custom versions of this 4.3-10 male to 4.3-10 male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA31068-FT3 L-com 4.3-10 Male to 7/16 DIN Male Low PIM Cable Using TFT-402-LF Coax Using Times Microwave Components 3 Foot data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.





LCCA31068-FT3

Electrical Specifications

Minimum	Typical	Maximum	Units
DC		5.8	GHz
		1.4:1	
	76		%
80			dB
		-160	dBc
	26.7 [87.6]		pF/ft [pF/m]
	DC	DC 76	DC 5.8 1.4:1 76 80 -160

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	5.8	GHz
Insertion Loss (Typ.)	0.33	0.42	0.56	0.83	1.23	dB

Electrical Specification Notes:

PIM test results vary between cables

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1*SQRT(FGHz) dB for the 4.3-10 connector and 0.1 dB for the 7/16 DIN connector.

Mechanical Specifications

Cable Assembly

 Length
 36 in [914.4 mm]

 Diameter
 0.5 in [12.7 mm]

 Weight
 0.145 lbs [65.77 g]

Cable

Cable Type TFT-5G-402
Impedance 50 Ohms
Inner Conductor Type Solid
Inner Conductor Material and Plating Copper
Dielectric Type PTFE
Number of Shields 2
Jacket Material FEP, Blue

Jacket Diameter 0.16 in [4.06 mm]

One Time Minimum Bend Radius 0.75 in [19.05 mm]



LCCA31068-FT3

Connectors

Description	Connector 1	Connector 2	
Туре	4.3-10 Male	7/16 DIN Male	
Impedance	50 Ohms	50 Ohms	
Mating Cycles	500		
Contact Material and Plating	Brass, Silver	Brass, Silver	
Contact Plating Specification	200 μin	5 μm	
Dielectric Type	PTFE	PTFE	
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal	
Body Plating Specification	80 μin	3 μm	
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal	
Coupling Nut Plating Specification	80 μin	3 μm	
Torque	44 in-lbs 4.97 Nm	22.083 ft-lbs 29.95 Nm	

Environmental Specifications Temperature

Operating Range

-55 to +85 deg C

Compliance Certifications (see product page for current document)


Plotted and Other Data

Notes:



LCCA31068-FT3

How to Order



Example: LCCA31068-12 = 12 inches long cable

LCCA31068-100cm = 100 cm long cable

4.3-10 Male to 7/16 DIN Male Low PIM Cable Using TFT-402-LF Coax Using Times Microwave Components 3 Foot from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

