

LCCA31069-M3

Configuration

Connector 1: 4.3-10 Male
Connector 2: N Male
Cable Type: TFT-5G-402
Coax Flex Type: Flexible

Features

- · 100% Tested with PIM Test Results Marked on Cable
- · Lightweight and Extremely Flexible
- · Low Loss with Excellent VSWR
- IP67 (when mated)
- Using Times Microwave Components



Applications

- Distributed Antenna Systems (DAS)
- Plenum Installations

- Multi-Carrier Communication Systems
- · PIM Testing

Description

L-com's LCCA31069-M3 is a 4.3-10 male to N male low PIM cable using TFT-5G-402 coax using Times Microwave components 3 meter and ships same-day. The TFT-5G-402 coax of this 4.3-10 cable uses the PTFE dielectric with a VoP of 76%. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com 4.3-10 to N cable assembly has a male to male gender configuration with flexible TFT-5G-402 series coax and operates to 5.8 GHz. The double shield of this 4.3-10 cable is layered by over providing shielding effectiveness greater than 80dB. With passive intermodulation levels better than -160 dBc, our cable assembly design is ideal where low PIM is desired. Times Microwave cable is used in each assembly and TMS components are used to form connections with the super flexible low PIM cable. These cable assemblies are expertly built to satisfy your specific need with high quality Times Microwave Systems manufactured parts.

Custom versions of this 4.3-10 male to N male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA31069-M3 L-com 4.3-10 Male to N Male Low PIM Cable Using TFT-5G-402 Coax Using Times Microwave Components 3 Meter data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
VSWR			1.4:1	
Velocity of Propagation		76		%
RF Shielding	80			dB
Passive Intermodulation			-160	dBc
IM3 (2x43dBm Tones) at 850 MHz or 1900 MHz				





LCCA31069-M3

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Capacitance		26.7 [87.6]		pF/ft [pF/m]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	5.8	GHz
Insertion Loss (Typ.)	0.67	0.96	1.36	2.19	3.39	dB

Electrical Specification Notes:

PIM test results vary between cables

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1*SQRT(FGHz) dB per connector.

Mechanical Specifications

Cable Assembly

 Length
 118.11 in [300 cm]

 Width/Diameter
 0.5 in [12.7 mm]

 Weight
 0.337 lbs [152.86 g]

Cable

Cable Type TFT-5G-402
Impedance 50 Ohms
Inner Conductor Type Solid
Inner Conductor Material and Plating Copper
Dielectric Type PTFE
Number of Shields 2

Number of Shields 2
Jacket Material FEP, Blue
Jacket Diameter 0.16 in [4

Jacket Diameter0.16 in [4.06 mm]One Time Minimum Bend Radius0.75 in [19.05 mm]





LCCA31069-M3

Connectors

Description	Connector 1	Connector 2
Туре	4.3-10 Male	N Male
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Mating Cycles	500	500
Contact Material and Plating	Brass, Silver	Brass, Silver
Contact Plating Specification	200 μin	200 μin
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Specification	80 μin	80 μin
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Coupling Nut Plating Specification	80 μin	80 μin
Torque	44 in-lbs 4.97 Nm	15 in-lbs 1.7 Nm

Environmental Specifications

Operating Range Temperature

-40 to +85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:






LCCA31069-M3

Typical Performance Data

How to Order



Example: LCCA31069-12 = 12 inches long cable

LCCA31069-100cm = 100 cm long cable

4.3-10 Male to N Male Low PIM Cable Using TFT-5G-402 Coax Using Times Microwave Components 3 Meter from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: https://www.l-com.com/4.3-10-male-n-male-cable-assembly-lcca31069-M3-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

