

#### LCCA9923

#### Configuration

Connector 1: N Female BulkheadConnector 2: N Female Bulkhead

Cable Type: LMR-240-UFCoax Flex Type: Flexible

#### **Description**

L-com's LCCA9923 is a low loss N female bulkhead to N female bulkhead cable assembly using LMR-240-UF coax with Times Microwave components with heatshrink and ships same-day. The LMR-240-UF coax of this N cable uses the PE (F) dielectric with a VoP of 84%, resulting in very low insertion loss compared to solid dielectrics. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com N to N cable assembly has a female to female gender configuration with flexible LMR-240-UF series coax and operates to 5.8 GHz. The double shield of this N cable is layered by tinned copper braid over aluminum tape providing shielding effectiveness greater than 90dB. L-com's RF cable assembly with N bulkhead interface enables system designers to have external connections on their product enclosures or to be used for other rack mount and panel mount applications.

Custom versions of this N female to N female cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA9923 L-com Low Loss N Female Bulkhead to N Female Bulkhead Cable Assembly using LMR-240-UF Coax With Times Microwave Components with HeatShrink data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

### **Electrical Specifications**

·				
Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
VSWR			1.5:1	
Velocity of Propagation		84		%
RF Shielding	90			dB
Group Delay		1.21 [3.97]		ns/ft [ns/m]
Capacitance		24.2 [79.4]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		4.28 [14.04]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		3.89 [12.76]		Ohms/1000ft [Ohms/Km]
Dielectric Withstanding Voltage (DC)			1,500	Vdc
Jacket Spark			5,000	Vrms
Input Power (Peak)			5.6	KWatts

#### Specifications by Frequency



### LCCA9923

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	250	500	1000	2500	5800	MHz	
LCCA9923	Custom Lengths	Insertion Loss (Typ.)	0.046	0.066	0.095	0.155	0.244	dB/ft	
ECCA3323	Available	ilisertion Loss (Typ.)	0.16	0.22	0.32	0.51	0.81	dB/m	
LCCA9923-12	12 inch	Insertion Loss (Typ.)	0.25	0.27	0.3	0.36	0.45	dB	0.216
LCCA9923-24	24 inch	Insertion Loss (Typ.)	0.3	0.34	0.39	0.51	0.69	dB	0.249
LCCA9923-36	36 inch	Insertion Loss (Typ.)	0.34	0.4	0.49	0.67	0.94	dB	0.281
LCCA9923-60	60 inch	Insertion Loss (Typ.)	0.43	0.53	0.68	0.98	1.42	dB	0.345
LCCA9923-300	300 inch	Insertion Loss (Typ.)	1.35	1.85	2.58	4.08	6.3	dB	0.985

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:0.1 dBLoss due to Connector 2:0.1 dBBase Weight:0.216 poundsAdditional Weight per Inch:0.00267 pounds

#### **Mechanical Specifications**

#### Cable Assembly

 Width/Diameter
 0.5 in [12.7 mm]

 Weight
 0.216 lbs [97.98 g]

#### Cable

Cable TypeLMR-240-UFImpedance50 OhmsInner Conductor TypeStrandedInner Conductor Material and PlatingCopperDielectric TypePE (F)Number of Shields2

Shield Layer 1 Aluminum Tape
Shield Layer 2 Tinned Copper Braid
Jacket Material TPE

Jacket Diameter 0.24 in [6.1 mm]

One Time Minimum Bend Radius0.75 in [19.05 mm]Repeated Minimum Bend Radius2.5 in [63.5 mm]Bending Moment0.13 lbs-ft [0.18 N-m]



## LCCA9923

#### **Connectors**

Description	Connector 1	Connector 2		
Туре	N Female Bulkhead	N Female Bulkhead		
Specification	MIL-STD-348	MIL-STD-348		
Impedance	50 Ohms	50 Ohms		
Configuration	Straight	Straight		
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold		
Dielectric Type	PTFE	PTFE		
Outer Conductor Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal		
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal		

### **Environmental Specifications**

Operating Range Temperature

-40 to +85 deg C

Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

Notes:

Values at 25°C, sea level.





#### LCCA9923

### **Typical Performance Data**

#### **How to Order**

Part Number Configuration:

LCCA9923 - xx uu

Unit of Measure:
cm = Centimeters
<br/>
<br/>
<br/>
<br/>
Length
Base Number

Example: LCCA9923-12 = 12 inches long cable

LCCA9923-100cm = 100 cm long cable

Low Loss N Female Bulkhead to N Female Bulkhead Cable Assembly using LMR-240-UF Coax With Times Microwave Components with HeatShrink from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: https://www.l-com.com/n-female-n-female-cable-assembly-invalid-lcca9923-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

# LCCA9923 CAD Drawing

Low Loss N Female Bulkhead to N Female Bulkhead Cable Assembly using LMR-240-UF Coax With Times Microwave Components with HeatShrink

