



## **LCCA9928**

### Configuration

· Connector 1: N Female Bulkhead

Connector 2: TNC MaleCable Type: LMR-240-UFCoax Flex Type: Flexible

# **Description**

L-com's LCCA9928 is a low loss N female bulkhead to TNC male cable assembly using LMR-240-UF coax with Times Microwave components with heatshrink and ships same-day. The LMR-240-UF coax of this N cable uses the PE (F) dielectric with a VoP of 84%, resulting in very low insertion loss compared to solid dielectrics. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com N to TNC cable assembly has a female to male gender configuration with flexible LMR-240-UF series coax and operates to 5.8 GHz. The double shield of this N cable is layered by tinned copper braid over aluminum tape providing shielding effectiveness greater than 90dB. L-com's RF cable assembly with N bulkhead interface enables system designers to have external connections on their product enclosures or to be used for other rack mount and panel mount applications.

Custom versions of this N female to N male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA9928 L-com Low Loss N Female Bulkhead to TNC Male Cable Assembly using LMR-240-UF Coax With Times Microwave Components with HeatShrink data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

# **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC	Тургост	5.8	GHz
VSWR			1.5:1	
Velocity of Propagation		84		%
RF Shielding	90			dB
Group Delay		1.21 [3.97]		ns/ft [ns/m]
Capacitance		24.2 [79.4]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		4.28 [14.04]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		3.89 [12.76]		Ohms/1000ft [Ohms/Km]
Dielectric Withstanding Voltage (DC)			1,500	Vdc
Jacket Spark			5,000	Vrms
Input Power (Peak)			5.6	KWatts

# Specifications by Frequency



# **LCCA9928**

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	250	500	1000	2500	5800	MHz	
LCCA9928	Custom Lengths	Insertion Loss (Typ.)	0.046	0.066	0.095	0.155	0.244	dB/ft	
ECCA9928	Available	insertion Loss (Typ.)	0.16	0.22	0.32	0.51	0.81	dB/m	
LCCA9928-12	12 inch	Insertion Loss (Typ.)	0.25	0.27	0.3	0.36	0.45	dB	0.175
LCCA9928-24	24 inch	Insertion Loss (Typ.)	0.3	0.34	0.39	0.51	0.69	dB	0.208
LCCA9928-36	36 inch	Insertion Loss (Typ.)	0.34	0.4	0.49	0.67	0.94	dB	0.24
LCCA9928-60	60 inch	Insertion Loss (Typ.)	0.43	0.53	0.68	0.98	1.42	dB	0.304
LCCA9928-300	300 inch	Insertion Loss (Typ.)	1.35	1.85	2.58	4.08	6.3	dB	0.944

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB Loss due to Connector 2: 0.1 dB Base Weight: 0.175 pounds Additional Weight per Inch: 0.00267 pounds

# **Mechanical Specifications**

## **Cable Assembly**

Width/Diameter 0.5 in [12.7 mm] Weight 0.175 lbs [79.38 g]

#### Cable

LMR-240-UF Cable Type Impedance 50 Ohms Inner Conductor Type Stranded Inner Conductor Material and Plating Copper Dielectric Type PE(F) Number of Shields

Shield Layer 1 Aluminum Tape Shield Layer 2 Tinned Copper Braid Jacket Material TPE

Jacket Diameter

0.24 in [6.1 mm] One Time Minimum Bend Radius 0.75 in [19.05 mm] Repeated Minimum Bend Radius 2.5 in [63.5 mm] **Bending Moment** 0.13 lbs-ft [0.18 N-m]



# **LCCA9928**

### **Connectors**

Description	Connector 1	Connector 2		
Туре	N Female Bulkhead	TNC Male		
Specification	MIL-STD-348			
Impedance	50 Ohms	50 Ohms		
Configuration	Straight	Straight		
Contact Material and Plating	Beryllium Copper, Gold	Brass, Gold		
Dielectric Type	PTFE	Teflon		
Outer Conductor Material and Plating	Brass, Tri-Metal			
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal		
Coupling Nut Material and Plating		Brass, Tri-Metal		

# **Environmental Specifications**

Operating Range Temperature

-40 to +85 deg C

**Compliance Certifications** (see product page for current document)

### **Plotted and Other Data**

Notes:

Values at 25°C, sea level.





## **LCCA9928**

# **Typical Performance Data**

#### **How to Order**

Part Number Configuration:

LCCA9928 - xx uu

Unit of Measure:
cm = Centimeters
<br/>
<br/>
<br/>
<br/>
Length
Base Number

Example: LCCA9928-12 = 12 inches long cable

LCCA9928-100cm = 100 cm long cable

Low Loss N Female Bulkhead to TNC Male Cable Assembly using LMR-240-UF Coax With Times Microwave Components with HeatShrink from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: https://www.l-com.com/n-female-tnc-male-cable-assembly-invalid-lcca9928-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

# LCCA9928 CAD Drawing

Low Loss N Female Bulkhead to TNC Male Cable Assembly using LMR-240-UF Coax With Times Microwave Components with HeatShrink

