

Low Loss 4.3-10 Male to 4.3-10 Male Cable Assembly using LMR-400-UF Coax With Times Microwave Components with HeatShrink



LCCA9943

Configuration

- Connector 1: 4.3-10 Male
- Connector 2: 4.3-10 Male
- Cable Type: LMR-400-UF
- Coax Flex Type: Flexible

Description

L-com's LCCA9943 is a low loss 4.3-10 male to 4.3-10 male cable assembly using LMR-400-UF coax with Times Microwave components with heatshrink and ships same-day. The LMR-400-UF coax of this 4.3-10 cable uses the PE (F) dielectric with a VoP of 85%, resulting in very low insertion loss compared to solid dielectrics. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com 4.3-10 to 4.3-10 cable assembly has a male to male gender configuration with flexible LMR-400-UF series coax and operates to 5.8 GHz. The double shield of this 4.3-10 cable is layered by tinned copper braid over aluminum tape providing shielding effectiveness greater than 90dB.

Custom versions of this 4.3-10 male to 4.3-10 male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA9943 L-com Low Loss 4.3-10 Male to 4.3-10 Male Cable Assembly using LMR-400-UF Coax With Times Microwave Components with HeatShrink data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
VSWR			1.5:1	
Velocity of Propagation		85		%
RF Shielding	90			dB
Group Delay		1.2 [3.94]		ns/ft [ns/m]
Capacitance		23.9 [78.41]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		1.07 [3.51]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		1.65 [5.41]		Ohms/1000ft [Ohms/Km]
Dielectric Withstanding Voltage (DC)			2,500	Vdc
Jacket Spark			8,000	Vrms
Input Power (Peak)			16	KWatts

Specifications by Frequency

Low Loss 4.3-10 Male to 4.3-10 Male Cable
Assembly using LMR-400-UF Coax With Times
Microwave Components with HeatShrink



LCCA9943

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	250	500	1000	2500	5800	MHz	
LCCA9943	Custom Lengths Available	Insertion Loss (Typ.)	0.023	0.034	0.049	0.081	0.13	dB/ft	
			0.08	0.12	0.17	0.27	0.43	dB/m	
LCCA9943-FT1	12 inch	Insertion Loss (Typ.)	0.13	0.18	0.25	0.4	0.62	dB	0.279
LCCA9943-FT2	24 inch	Insertion Loss (Typ.)	0.15	0.21	0.3	0.48	0.75	dB	0.366
LCCA9943-FT3	36 inch	Insertion Loss (Typ.)	0.17	0.25	0.35	0.56	0.88	dB	0.453
LCCA9943-FT5	60 inch	Insertion Loss (Typ.)	0.22	0.32	0.45	0.73	1.14	dB	0.627
LCCA9943-FT25	300 inch	Insertion Loss (Typ.)	0.68	1	1.43	2.35	3.74	dB	2.367

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1*sqrt(fGHz) dB

Loss due to Connector 2: 0.1*sqrt(fGHz) dB

Base Weight: 0.279 pounds

Additional Weight per Inch: 0.00725 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter

0.5 in [12.7 mm]

Weight

0.279 lbs [126.55 g]

Cable

Cable Type

LMR-400-UF

Inner Conductor Type

Stranded

Inner Conductor Material and Plating

Copper

Dielectric Type

PE (F)

Number of Shields

2

Shield Layer 1

Aluminum Tape

Shield Layer 2

Tinned Copper Braid

Jacket Material

TPE

Jacket Diameter

0.405 in [10.29 mm]

One Time Minimum Bend Radius

1 in [25.4 mm]

Repeated Minimum Bend Radius

4 in [101.6 mm]

Bending Moment

0.38 lbs-ft [0.52 N-m]

Flat Plate Crush

20 lbs/in [0.36 Kg/mm]

Tensile Strength

160 lbs [72.57 Kg]

Low Loss 4.3-10 Male to 4.3-10 Male Cable
Assembly using LMR-400-UF Coax With Times
Microwave Components with HeatShrink



LCCA9943

Connectors

Description	Connector 1	Connector 2
Type	4.3-10 Male	4.3-10 Male
Configuration	Straight	Straight
Mating Cycles	500	500
Contact Material and Plating	Brass, Silver	Brass, Silver
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Seal Gasket Material	Silicone	Silicone

Environmental Specifications

Operating Range Temperature -40 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:
Values at 25°C, sea level.

Low Loss 4.3-10 Male to 4.3-10 Male Cable Assembly using LMR-400-UF Coax With Times Microwave Components with HeatShrink



LCCA9943

Typical Performance Data

How to Order

Part Number Configuration:

LCCA9943

- xx

uu

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: LCCA9943-12 = 12 inches long cable
LCCA9943-100cm = 100 cm long cable

Low Loss 4.3-10 Male to 4.3-10 Male Cable Assembly using LMR-400-UF Coax With Times Microwave Components with HeatShrink from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/4.3-10-male-4.3-10-male-cable-lcca9943-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

LCCA9943 CAD Drawing
Low Loss 4.3-10 Male to 4.3-10 Male Cable Assembly using LMR-400-UF Coax With Times Microwave Components with HeatShrink

