

OptiMOS® Power-Transistor





Product Summary

V_{DS}	55	V
$R_{DS(on),max}^{3)}$	65	mΩ
I_D	20	A

Features

- Dual N-channel Logic Level - Enhancement mode
- AEC Q101 qualified
- MSL1 up to 260°C peak reflow
- 175°C operating temperature
- Green Product (RoHS compliant)
- 100% Avalanche tested
- Feasible for automatic optical inspection (AOI)

PG-TDSON-8



Type	Package	Marking
IPG20N06S2L-65A	PG-TDSON-8	2N06L65

Maximum ratings, at $T_J=25\text{ °C}$, unless otherwise specified

Parameter	Symbol	Conditions	Value	Unit
Continuous drain current one channel active ¹⁾	I_D	$T_C=25\text{ °C}$, $V_{GS}=10\text{ V}$	20	A
		$T_C=100\text{ °C}$, $V_{GS}=10\text{ V}$	14	
Pulsed drain current ¹⁾ one channel active	$I_{D,pulse}$	-	80	
Avalanche energy, single pulse ^{1, 3)}	E_{AS}	$I_D=10\text{ A}$	40	mJ
Avalanche current, single pulse ³⁾	I_{AS}	-	15	A
Gate source voltage	V_{GS}	-	±20	V
Power dissipation one channel active	P_{tot}	$T_C=25\text{ °C}$	43	W
Operating and storage temperature	T_J , T_{stg}	-	-55 ... +175	°C
IEC climatic category; DIN IEC 68-1	-	-	55/175/56	

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	

Thermal characteristics¹⁾

Thermal resistance, junction - case	R_{thJC}	-	-	-	3.5	K/W
SMD version, device on PCB	R_{thJA}	minimal footprint	-	100	-	
		6 cm ² cooling area ²⁾	-	60	-	

Electrical characteristics, at $T_j=25\text{ °C}$, unless otherwise specified

Static characteristics

Drain-source breakdown voltage	$V_{(BR)DSS}$	$V_{GS}=0\text{ V}, I_D=1\text{ mA}$	55	-	-	V
Gate threshold voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=14\text{ }\mu\text{A}$	1.2	1.6	2.0	
Zero gate voltage drain current ³⁾	I_{DSS}	$V_{DS}=55\text{ V}, V_{GS}=0\text{ V}, T_j=25\text{ °C}$	-	0.01	1	μA
		$V_{DS}=55\text{ V}, V_{GS}=0\text{ V}, T_j=125\text{ °C}^{2)}$	-	1	100	
Gate-source leakage current ³⁾	I_{GSS}	$V_{GS}=20\text{ V}, V_{DS}=0\text{ V}$	-	1	100	nA
Drain-source on-state resistance ³⁾	$R_{DS(on)}$	$V_{GS}=4.5\text{ V}, I_D=7.5\text{ A}$	-	67	79	m Ω
		$V_{GS}=10\text{ V}, I_D=15\text{ A}$	-	53	65	

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	

Dynamic characteristics¹⁾

Input capacitance ³⁾	C_{iss}	$V_{GS}=0\text{ V}, V_{DS}=25\text{ V},$ $f=1\text{ MHz}$	-	315	410	pF
Output capacitance ³⁾	C_{oss}		-	90	120	
Reverse transfer capacitance ³⁾	C_{rss}		-	35	50	
Turn-on delay time	$t_{d(on)}$	$V_{DD}=27.5\text{ V},$ $V_{GS}=10\text{ V}, I_D=20\text{ A},$ $R_{G,ext}=11\text{ }\Omega$	-	2	-	ns
Rise time	t_r		-	3	-	
Turn-off delay time	$t_{d(off)}$		-	10	-	
Fall time	t_f		-	7	-	

Gate Charge Characteristics^{1, 3)}

Gate to source charge	Q_{gs}	$V_{DD}=44\text{ V}, I_D=20\text{ A},$ $V_{GS}=0\text{ to }10\text{ V}$	-	1.2	1.6	nC
Gate to drain charge	Q_{gd}		-	3.5	5.3	
Gate charge total	Q_g		-	9.4	12	
Gate plateau voltage	$V_{plateau}$		-	3.9	-	V

Reverse Diode


Diode continuous forward current ¹⁾ one channel active	I_S	$T_C=25\text{ }^\circ\text{C}$	-	-	20	A
Diode pulse current ¹⁾ one channel active	$I_{S,pulse}$		-	-	80	
Diode forward voltage	V_{SD}	$V_{GS}=0\text{ V}, I_F=15\text{ A},$ $T_J=25\text{ }^\circ\text{C}$	-	1.0	1.3	V
Reverse recovery time ¹⁾	t_{rr}	$V_R=27.5\text{ V}, I_F=I_S,$ $di_F/dt=100\text{ A}/\mu\text{s}$	-	30	-	ns
Reverse recovery charge ^{1, 3)}	Q_{rr}		-	28	-	nC

¹⁾ Specified by design. Not subject to production test.


²⁾ Device on 40 mm x 40 mm x 1.5 mm epoxy PCB FR4 with 6 cm² (one layer, 70 μm thick) copper area for drain connection. PCB is vertical in still air.

³⁾ Per channel


1 Power dissipation

 $P_{\text{tot}} = f(T_C); V_{\text{GS}} \geq 6 \text{ V}; \text{ one channel active}$



2 Drain current

 $I_D = f(T_C); V_{\text{GS}} \geq 6 \text{ V}; \text{ one channel active}$


3 Safe operating area


 $I_D = f(V_{\text{DS}}); T_C = 25^\circ\text{C}; D = 0; \text{ one channel active}$
parameter: t_p


4 Max. transient thermal impedance

 $Z_{\text{thJC}} = f(t_p)$
parameter: $D = t_p/T$



5 Typ. output characteristics³⁾

 $I_D = f(V_{DS}); T_j = 25\text{ °C}$

parameter: V_{GS}



6 Typ. drain-source on-state resistance³⁾

 $R_{DS(on)} = f(I_D); T_j = 25\text{ °C}$


parameter: V_{GS}


7 Typ. transfer characteristics³⁾

 $I_D = f(V_{GS}); V_{DS} = 6\text{ V}$

parameter: T_j



8 Typ. drain-source on-state resistance³⁾

 $R_{DS(on)} = f(T_j); I_D = 15\text{ A}; V_{GS} = 10\text{ V}$


9 Typ. gate threshold voltage


$$V_{GS(th)} = f(T_j); V_{GS} = V_{DS}$$

parameter: I_D



10 Typ. Capacitances³⁾


$$C = f(V_{DS}); V_{GS} = 0 \text{ V}; f = 1 \text{ MHz}$$



11 Typical forward diode characteristics³⁾

$$I_F = f(V_{SD})$$


parameter: T_j



12 Avalanche characteristics³⁾

$$I_{AS} = f(t_{AV})$$


parameter: $T_{j(start)}$



13 Avalanche energy³⁾


$$E_{AS} = f(T_j)$$

parameter: I_D



14 Drain-source breakdown voltage


$$V_{BR(DSS)} = f(T_j); I_D = 1 \text{ mA}$$




15 Typ. gate charge³⁾

$$V_{GS} = f(Q_{gate}); I_D = 20 \text{ A pulsed}$$

parameter: V_{DD}



16 Gate charge waveforms



Published by
Infineon Technologies AG
81726 Munich, Germany

© Infineon Technologies AG 2012
All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances.

For information on the types in question, please contact the nearest Infineon Technologies Office.

Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life.

If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

Revision History

Version	Date	Changes
Revision 1.0	20.09.2012	Final Data Sheet
Revision 1.01	02.08.2024	Package naming updated