International
IOR Rectifier

PD - 95762

IRLMS1503PbF

HEXFET® Power MOSFET

- Generation V Technology
- Micro6 Package Style
- Ultra Low $R_{DS(on)}$
- N-Channel MOSFET
- Lead-Free



Top View

V_{DSS} = 30V

$R_{DS(on)}$ = 0.10Ω


Micro6™

Description

Fifth Generation HEXFET® power MOSFETs from International Rectifier utilize advanced processing techniques to achieve extremely low on-resistance per silicon area. This benefit, combined with the fast switching speed and ruggedized device design that HEXFET® power MOSFETs are well known for, provides the designer with an extremely efficient and reliable device for use in a wide variety of applications.

The Micro6™ package with its customized leadframe produces a HEXFET® power MOSFET with $R_{DS(on)}$ 60% less than a similar size SOT-23. This package is ideal for applications where printed circuit board space is at a premium. It's unique thermal design and $R_{DS(on)}$ reduction enables a current-handling increase of nearly 300% compared to the SOT-23.

Absolute Maximum Ratings

	Parameter	Max.	Units
I_D @ T_A = 25°C	Continuous Drain Current, V_{GS} @ 10V	3.2	A
I_D @ T_A = 70°C	Continuous Drain Current, V_{GS} @ 10V	2.6	
I_{DM}	Pulsed Drain Current ①	18	
P_D @T_A = 25°C	Power Dissipation	1.7	W
	Linear Derating Factor	13	mW/°C
V_{GS}	Gate-to-Source Voltage	± 20	V
dv/dt	Peak Diode Recovery dv/dt ②	5.0	V/ns
T_J, T_{STG}	Junction and Storage Temperature Range	-55 to + 150	°C

Thermal Resistance Ratings

	Parameter	Min.	Typ.	Max	Units
$R_{\theta JA}$	Maximum Junction-to-Ambient ④	—	—	75	°C/W

Electrical Characteristics @ T_J = 25°C (unless otherwise specified)

	Parameter	Min.	Typ.	Max.	Units	Conditions
$V_{(BR)DSS}$	Drain-to-Source Breakdown Voltage	30	–––	–––	V	V_{GS} = 0V, I_D = 250µA
$\Delta V_{(BR)DSS}/\Delta T_J$	Breakdown Voltage Temp. Coefficient	–––	0.037	–––	V/°C	Reference to 25°C, I_D = 1mA
$R_{DS(on)}$	Static Drain-to-Source On-Resistance	–––	–––	0.100	Ω	V_{GS} = 10V, I_D = 2.2A ③
		–––	–––	0.20		V_{GS} = 4.5V, I_D = 1.1A ③
$V_{GS(th)}$	Gate Threshold Voltage	1.0	–––	–––	V	V_{DS} = V_{GS}, I_D = 250µA
g_{fs}	Forward Transconductance	1.1	–––	–––	S	V_{DS} = 10V, I_D = 1.1A
I_{DSS}	Drain-to-Source Leakage Current	–––	–––	1.0	µA	V_{DS} = 24V, V_{GS} = 0V
		–––	–––	25		V_{DS} = 24V, V_{GS} = 0V, T_J = 125°C
I_{GSS}	Gate-to-Source Forward Leakage	–––	–––	-100	nA	V_{GS} = -20V
	Gate-to-Source Reverse Leakage	–––	–––	100		V_{GS} = 20V
Q_g	Total Gate Charge	–––	6.4	9.6	nC	I_D = 2.2A
Q_{gs}	Gate-to-Source Charge	–––	1.1	1.7		V_{DS} = 24V
Q_{gd}	Gate-to-Drain ("Miller") Charge	–––	1.9	2.8		V_{GS} = 10V, See Fig. 6 and 9 ③
$t_{d(on)}$	Turn-On Delay Time	–––	4.6	–––	ns	V_{DD} = 15V
t_r	Rise Time	–––	4.4	–––		I_D = 2.2A
$t_{d(off)}$	Turn-Off Delay Time	–––	10	–––		R_G = 6.0Ω
t_f	Fall Time	–––	2.0	–––		R_D = 6.7Ω, See Fig. 10 ③
C_{iss}	Input Capacitance	–––	210	–––	pF	V_{GS} = 0V
C_{oss}	Output Capacitance	–––	90	–––		V_{DS} = 25V
C_{rss}	Reverse Transfer Capacitance	–––	32	–––		f = 1.0MHz, See Fig. 5

Source-Drain Ratings and Characteristics

	Parameter	Min.	Typ.	Max.	Units	Conditions
I_S	Continuous Source Current (Body Diode)	–––	–––	1.7	A	MOSFET symbol showing the integral reverse p-n junction diode. 
I_{SM}	Pulsed Source Current (Body Diode) ①	–––	–––	18		
V_{SD}	Diode Forward Voltage	–––	–––	1.2	V	T_J = 25°C, I_S = 2.2A, V_{GS} = 0V ③
t_{rr}	Reverse Recovery Time	–––	36	54	ns	T_J = 25°C, I_F = 2.2A
Q_{rr}	Reverse RecoveryCharge	–––	39	58	nC	di/dt = 100A/µs ③

Notes:

① Repetitive rating; pulse width limited by max. junction temperature. (See fig. 11)

② I_{SD} ≤ 2.2A, di/dt ≤ 150A/µs, V_{DD} ≤ $V_{(BR)DSS}$, T_J ≤ 150°C

③ Pulse width ≤ 300µs; duty cycle ≤ 2%.

④ Surface mounted on FR-4 board, t ≤ 5sec.



Fig 1. Typical Output Characteristics



Fig 2. Typical Output Characteristics



Fig 3. Typical Transfer Characteristics



Fig 4. Normalized On-Resistance Vs. Temperature



Fig 5. Typical Capacitance Vs. Drain-to-Source Voltage



Fig 6. Typical Gate Charge Vs. Gate-to-Source Voltage



Fig 7. Typical Source-Drain Diode Forward Voltage



Fig 8. Maximum Safe Operating Area



Fig 9a. Basic Gate Charge Waveform



Fig 10a. Switching Time Test Circuit



Fig 9b. Gate Charge Test Circuit



Fig 10b. Switching Time Waveforms



Fig 11. Maximum Effective Transient Thermal Impedance, Junction-to-Ambient



Fig 13. For N-channel HEXFET® power MOSFET s

Micro6 (SOT23 6L) Package Outline

Dimensions are shown in milimeters (inches)



NOTES :
1. DIMENSIONING & TOLERANCING PER ANSI Y14.5M-1982.
2. CONTROLLING DIMENSION : MILLIMETER.
3. DIMENSIONS ARE SHOWN IN MILLIMETERS (INCHES).

Micro6 (SOT23 6L) Part Marking Information



PART NUMBER CODE REFERENCE:

A = IRLMS1902
B = IRLMS1503
C = IRLMS6702
D = IRLMS5703
E = IRLMS6802
F = IRLMS4502
G = IRLMS2002
H = IRLMS6803

Note: A line above the work week
(as shown here) indicates Lead-Free.

W = (1-26) IF PRECEDED BY LAST DIGIT OF CALENDAR YEAR

YEAR	Y	WORK WEEK	W
2001	1	01	A
2002	2	02	B
2003	3	03	C
2004	4	04	D
2005	5		
2006	6		
2007	7		
2008	8		
2009	9		
2010	0	24	X
		25	Y
		26	Z

W = (27-52) IF PRECEDED BY A LETTER

YEAR	Y	WORK WEEK	W
2001	A	27	A
2002	B	28	B
2003	C	29	C
2004	D	30	D
2005	E		
2006	F		
2007	G		
2008	H		
2009	J		
2010	K	50	X
		51	Y
		52	Z

Micro6 Tape & Reel Information

Dimensions are shown in milimeters (inches)



NOTES :
1. OUTLINE CONFORMS TO EIA-481 & EIA-541.



NOTES:
1. CONTROLLING DIMENSION : MILLIMETER.
2. OUTLINE CONFORMS TO EIA-481 & EIA-541.

This product has been designed and qualified for the consumer market.
Qualification Standards can be found on IR's Web site.

Data and specifications subject to change without notice.

International
IOR Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105
TAC Fax: (310) 252-7903
Visit us at www.irf.com for sales contact information. 01/05

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie") .

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (**www.infineon.com**).

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.