


[Click here](#) for the 3D model.

### General Information

Series	T429 CWR29
Dielectric	MnO2 Tantalum
Style	SMD Chip
Description	SMD, MnO2, Molded, Military Equivalent, Low ESR
RoHS	No
Prop 65	<b>WARNING:</b> Cancer and reproductive harm - <a href="https://www.p65warnings.ca.gov/">https://www.p65warnings.ca.gov/</a> .
SCIP Number	652b281f-d242-4453-bc44-0655d646cec3
Termination	Hot Solder Dipped
Qualifications	MIL-PRF-55365/11, CWR29 Style
AEC-Q200	No
Typical Component Weight	349.01 mg
Notes	Note: When Option C Is Selected For Lead Material, Add An Additional 0.38mm To The Tolerances For "L", "W", "H", "K", "F" And "S".
MSL	1

### Dimensions

L	7.24mm +/-0.38mm	Capacitance	330 uF
W	3.81mm +/-0.38mm	Tolerance	10%
H	2.79mm +/-0.38mm	Voltage DC	6 VDC (85C), 4 VDC (125C)
S	1.27mm +0.25/-0.13mm	Temperature Range	-55/+125°C
F	3.68mm +0.13/-0.51mm	Rated Temperature	85°C
K	1.52mm MIN	Dissipation Factor	10% 120Hz 25C
P	0.76mm MIN	Failure Rate	C (0.01%/1000 Hrs)
		ESR	0.18 Ohms (100kHz 25C)
		Ripple Current	913 mA (rms, 100kHz 25C)
		Leakage Current	20 uA (5min 25°C)
		Testing and Reliability	Surge Testing (10 Cycles At -55C +/-5C And +85C +/-5C Before Weibull)

### Packaging Specifications

Packaging	T&R, 178mm	Capacitance	330 uF
Packaging Quantity	500	Tolerance	10%

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.