






Oct.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTE 1 Contact area : Gold plating 0.3μm min
Lead area : Gold plating 0.03μm min
Under : Nickel plating 2μm min
- NOTE 2 This product must be screwed to the board.
Please prepare the screws by the customer.
<SCREW REQUIREMENTS>
NOMINAL DIAMETER: M2.6 x 0.45
SCREW LENGTH : 1.8 ± 0.45 + BOARD thickness 't'

3	PBT	UL94V-0(BLACK)						
2	PBT	UL94V-0(BLACK)	5	STEEL	NICKEL PLATING			
1	PHOSPHOR BRONZE	1	4	ZINC ALLOY DIE CASTING	NICKEL PLATING			
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS			
UNITS mm		SCALE 2 : 1	COUNT 4	DESCRIPTION OF REVISIONS DIS-E-00010989	DESIGNED KG. OKITA	CHECKED MN. KENJO	DATE 20220908	
HIROSE ELECTRIC CO., LTD.		APPROVED : HO. MIWA	20050105	DRAWING NO.	EDC3-041443-01			
		CHECKED : YH. ENAMI	20050105	PART NO.	DX20M-20S(50)			
		DESIGNED : TU. TANIGUCHI	20050105	CODE NO.	CL0230-5013-8-50			
		DRAWN : TU. TANIGUCHI	20050105					1/1