




Oct.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Oct.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Oct.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



DIMENSION TABLE OF CONNECTOR, FPC, FFC, LAND PATTERN AND METAL MASK

| PART NO.           | CODE NO.        | *  | A    | B    | C     | D     | E     | F     | G    | H    | J    | K    |
|--------------------|-----------------|----|------|------|-------|-------|-------|-------|------|------|------|------|
| FH28-10S-0.5SH(98) | CL586-1861-4-98 | 10 | 4.5  | 9.9  | 5.57  | 6.15  | 7.35  | 9.58  | 5.5  | 7.1  | 10.6 | 7    |
| FH28-40S-0.5SH(98) | CL586-1803-8-98 | 40 | 19.5 | 24.9 | 20.57 | 21.15 | 22.35 | 24.58 | 20.5 | 22.1 | 25.6 | 22   |
| FH28-45S-0.5SH(98) | CL586-1848-6-98 | 45 | 22   | 27.4 | 23.07 | 23.65 | 24.85 | 27.08 | 23   | 24.6 | 28.1 | 24.5 |
| FH28-50S-0.5SH(98) | CL586-1801-2-98 | 50 | 24.5 | 29.9 | 25.57 | 26.15 | 27.35 | 29.58 | 25.5 | 27.1 | 30.6 | 27   |
| FH28-55S-0.5SH(98) | CL586-1800-0-98 | 55 | 27   | 32.4 | 28.07 | 28.65 | 29.85 | 32.08 | 28   | 29.6 | 33.1 | 29.5 |
| FH28-60S-0.5SH(98) | CL586-1811-6-98 | 60 | 29.5 | 34.9 | 30.57 | 31.15 | 32.35 | 34.58 | 30.5 | 32.1 | 35.6 | 32   |

DIMENSION TABLE OF DRAWING FOR PACKING

| PART NO.           | CODE NO.        | *  | L    | M    | N    | P    | Q  | R    | T    | S    |
|--------------------|-----------------|----|------|------|------|------|----|------|------|------|
| FH28-10S-0.5SH(98) | CL586-1861-4-98 | 10 | 5.5  | 10.3 | 11.5 | -    | 24 | 25.4 | 29.4 | 11.3 |
| FH28-40S-0.5SH(98) | CL586-1803-8-98 | 40 | 20.5 | 25.3 | 20.2 | 40.4 | 44 | 45.4 | 49.4 | -    |
| FH28-45S-0.5SH(98) | CL586-1848-6-98 | 45 | 23   | 27.8 | 20.2 | 40.4 | 44 | 45.4 | 49.4 | 28.8 |
| FH28-50S-0.5SH(98) | CL586-1801-2-98 | 50 | 25.5 | 30.3 | 20.2 | 40.4 | 44 | 45.4 | 49.4 | -    |
| FH28-55S-0.5SH(98) | CL586-1800-0-98 | 55 | 28   | 32.8 | 20.2 | 40.4 | 44 | 45.4 | 49.4 | -    |
| FH28-60S-0.5SH(98) | CL586-1811-6-98 | 60 | 30.5 | 35.3 | 26.2 | 52.4 | 56 | 57.4 | 61.4 | -    |

\* : NUMBER OF CONTACTS

|  |             |                   |
|--|-------------|-------------------|
|  | DRAWING NO. | EDC3-153887-07    |
|  | PART NO.    | FH28-*S-0.5SH(98) |
|  | CODE NO.    | CL586             |
|  |             | 3/3               |