



Oct.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




- Notes
- Part No. ⑤ is assembled into Part No. ①.
 - Part No. ②④ and ⑤ are not assembled when delivered.
 - Outer diameter of applicable cable is $\phi 9.2 \pm 0.3$.
 - Cable exit direction depends on the way connector unit is assembled.
 - Screw tightening torque shall be $0.22\text{N} \cdot \text{m}$.

Assembled Figure



③ The figure of cable exit direction (Free)



5	Steel	Over : Nickel Plating $2\mu\text{m}$ min. Under : Copper Plating $1\mu\text{m}$ min.	10	Steel	Over plating : Nickel Plating $1\mu\text{m}$ min. Under plating : Copper Plating $5\mu\text{m}$ min.
4	Stainless steel		9	PPS	Black , UL94V-0
3	Stainless steel		8	PPS	Black , UL94V-0
2	PC	Gray , UL94V-0	7	Phosphor bronze	Contact area : Gold Plating $0.3\mu\text{m}$ min. Lead : Tin Plating $1\mu\text{m}$ min.
1	PC	Gray , UL94V-0	6	Phosphor bronze	Under : Nickel Plating $2\mu\text{m}$ min.
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE 2 : 1	COUNT 2	DESCRIPTION OF REVISIONS DIS-E-00001697	DESIGNED P. EKSOURIYA
HIROSE ELECTRIC CO., LTD.		APPROVED : RI. TAKAYASU	12.07.25	DRAWING NO. EDC-122495-50-01	CHECKED RI. TAKAYASU
		CHECKED : EJ. WAKATSUKI	12.07.25	PART NO. FI40B-20S-CVS5(50)	DATE 18.07.23
		DESIGNED : TS. ITO	12.07.25	CODE NO. CL230-0535-6-50	
		DRAWN : TY. ITO	12.07.21		