






CONTACT ARRANGEMENTS
VIEWED FROM THE MATING SIDE



- NOTES
- 1 THE RECOMMENDED CLAMP TORQUE, REF. NO. ④ AND ⑩ : 1.5 N·m.
1 THREAD LOCKER TO THE THREADED PORTION OF REF. NO. ①
APPLIES TO PREVENT REF. NO. ④ FROM LOOSING.
RECOMMENDED THREAD LOCKER: LOCTITE 263, HENKEL JAPAN LTD.
REF. NO. ⑩ SHALL BE TIGHTENED BY TORQUE AFTER
CLAMPED UNTIL IT TOUCHES THE SURFACE B.
 - 2 ONE EXAMPLE OF THE ROTATION OF REF. NO. ①, ④ AND ⑩ ARE SHOWN.
 - 3 THE ASSEMBLY THIS PRODUCT APPLIES TO THE MANUAL ETAD-C0355-00.

5	POLYAMIDE				
4	BRASS	MATTE FINISH NICKEL PLATED	10	BRASS	MATTE FINISH NICKEL PLATED
3	BERYLLIUM COPPER	GOLD PLATING 0.2µm min. NICKEL UNDER PLATING 2µm min.	9	POLYAMIDE	
2	POLYAMIDE	(BLUE)	8	BRASS	MATTE FINISH NICKEL PLATED
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	7	STEEL	NICKEL PLATING
6	STAINLESS STEEL				
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2 : 1	COUNT 1 2	DESCRIPTION OF REVISIONS DIS-C-00016940	DESIGNED HT. ZENBA	CHECKED EJ. KUNII	DATE 20240214
APPROVED : MO. SATOH 20051024				DRAWING NO. EDC4-007759-73			
CHECKED : EJ. KUNII 20051021				PART NO. HR10-7P-6S(73)			
DESIGNED : DS. MATSUNE 20051019				CODE NO. CL0110-0024-4-73			
DRAWN : DS. MATSUNE 20051019				1 1			