


May.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES
- ① HAND CRIMPING TOOL. REF. NO. ⑨:
HR10A-TC-02 (CL150-0041-2)
 - ② THE HOLE DIAMETER FOR CRIMPING: $\phi 7.0$
 - ③ THE RECOMMENDED CLAMP TORQUE,
REF. NO. ⑦: 2 TO 2.5 N·m.
 - ④ ACROSS FLATS HEXAGON HEAD OF REF. NO. ⑧: 1.27
THE RECOMMENDED CLAMP TORQUE,
REF. NO. ⑧: 0.3 TO 0.4 N·m.
THE TIP OF REF. NO. ⑧ SHALL BE FIXED TO
THE CONCAVE PORTION WITH REF. NO. ⑨ CLAMPED
TO THE CABLE.
 - ⑤ LOCTITE 263, HENKEL JAPAN OR EQUIVALENT APPLIES
TO PREVENT REF. NO. ① AND ⑧ FOR LOOSENING.
 - ⑥ ONE EXAMPLE OF THE ROTATION OF REF. NO. ⑦ TO
REF. NO. ① IS SHOWN.
 - ⑦ THE CABLE PULL AND TWISTING STRENGTH AND
OTHER CHARACTERISTICS MAY DIFFER,
DEPENDING ON THE CABLE STRUCTURE.
PLEASE CONFIRM BEFORE THE USE.
 - ⑧ THE ASSEMBLY THIS PRODUCT APPLIES TO
THE MANUAL ETAD-C0354-00.

5	BRASS	MATTE FINISH NICKEL PLATED	10	CHLOROPRENE RUBBER	(BLACK)
4	PHOSPHOR BRONZE	OVER PLATING: GOLD 0.2 μ m min.	9	BRASS	
3	PHOSPHOR BRONZE	UNDER PLATING: NICKEL 2 μ m min.	8	STEEL	NICKEL PLATING M2.6X0.45X3
2	POLYAMIDE	(BLACK) UL94V-0	7	BRASS	NICKEL PLATING
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	6	STEEL	NICKEL PLATING
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2 : 1	COUNT ① 2	DESCRIPTION OF REVISIONS DIS-C-00016953	DESIGNED HT. ZENBA	CHECKED EJ. KUNII	DATE 20240220
APPROVED : MO. SATOH 20070411				DRAWING NO. EDC4-021367-74			
CHECKED : EJ. KUNII 20070411				PART NO. HR10A-10P-10S(74)			
DESIGNED : TO. HORII 20070411				CODE NO. CL0110-0408-6-74			
DRAWN : MK. SATO 20070324							