





B Detail of mounting guide



Panel cutout
(t=0.7 to 2)



△ Note 1 The recommended clamp torque of Ref.No. ⑦ to be 2N · m.
Loctite 243, Henkel Japan or equivalent apply to
prevent Ref.No. ⑦ from loosening.

△ CAD change

4	Brass	Silver plating 2μm min.			
3	Polyamide	(Black) UL94V-0	7	Brass	Nickel plating
2	Stainless steel		6	Phosphor bronze	Nickel plating
1	Zinc alloy	Matte finish nickel plated	5	Brass	Silver plating 2μm min.
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS

UNITS mm		SCALE 2:1	COUNT 2	DESCRIPTION OF REVISIONS DIS-C-00019773	DESIGNED TY. SUZUKI	CHECKED HY. KOBAYASHI	DATE 2025. 04. 25
HIROSE ELECTRIC CO., LTD.		APPROVED : MO. SATOH	2005. 10. 20	DRAWING NO. EDC-020553-73-73			
		CHECKED : EJ. KUNII	2005. 10. 20	PART NO. HR10A-10R-12P (73)			
		DESIGNED : DS. MATSUNE	2005. 10. 19	CODE NO. CL0110-0404-5-73			
		DRAWN : DS. MATSUNE	2005. 10. 19				