




B
Detail of mounting guide




Panel cutout
(t=0.7 to 2)



PCB Layout

(Indicates the side of the surface to which dip posts are inserted.)



- Note 1 The recommended clamp torque of Ref.No. ⑥ to be 2 N·m.
2 Loctite 243, Henkel Japan or equivalent apply to prevent Ref.No. ⑥ from loosening.

CAD change ②

3	Polybutylene terephthalate	(Black) UL94V-0	6	Brass	Nickel plating
2	Stainless steel		5	Phosphor bronze	Nickel plating
1	Zinc alloy	Matte finish nickel plated	4	Phosphor bronze	Silver plating 2μm min.
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS

UNITS mm		SCALE 2:1	COUNT ② 2	DESCRIPTION OF REVISIONS DIS-C-00020745	DESIGNED TY. SUZUKI	CHECKED HY. KOBAYASHI	DATE 2025. 10. 01
HIROSE ELECTRIC CO., LTD.		APPROVED : MR. YOSHIDA	2005. 01. 05	DRAWING NO. EDC-022533-71-71			
		CHECKED : MO. SATOH	2005. 01. 05	PART NO. HR10A-10R-12SB (71)			
		DESIGNED : YH. YAMADA	2005. 01. 05	CODE NO. CL0110-0415-1-71			
		DRAWN : YH. YAMADA	2005. 01. 05				