


1		2			3		4				
	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
▲	1	DIS-C-000585	T.K	E.K	07.07.27	▲					. .
▲						▲					. .
▲						▲					. .



NOTE 1 APPLICABLE CRIMP CONTACT:HR12-SC-212(CL112-0408-9)  
(WIRE RENG:AWG#26 TO 30  
JACKET DIAMETER:φ 1 MAX)  
APPLICABLE CRIMP CONTACT EXTRACTION TOOL:  
HR12-SC-TP(CL112-0050-3)  
② THE RECOMMENDED CLAMP TORQUE,REF.NO.④ :2N・m.  
LOCTITE 242,HENKEL OR EQUIVALENT IS RECOMMENDED TO PREVENT REF.NO. ④ FROM LOOSENING.

2	POLYBUTYLENE TEREPHTHALATE	(BLACK)	UL94V-0	4	BRASS ①	NICKEL PLATING
1	BRASS	NICKEL PLATING		3	PHOSPHOR BRONZE	NICKEL PLATING
NO.	MATERIAL	FINISH, REMARKS		NO.	MATERIAL	FINISH, REMARKS

CODE NO. (OLD) CL		DRAWN M.SATO '06 10 03	DESIGNED T.KOMATSU '06 10 04	CHECKED E.KUNII '06 10 04	APPROVED M.SATO '06 10 06	RELEASED
----------------------	--	------------------------------	------------------------------------	---------------------------------	---------------------------------	----------

 SCALE 2 : 1 UNITS mm	DRAWING NO. EDC4-043235-73 <b>HRS</b> HIROSE ELECTRIC CO.,LTD.	PART NO. HR10A-10TR-12SC(73) CODE NO. CL110-0456-9-73	1 1
-----------------------------------	---	--	--------