



- NOTE 1 APPLICABLE CRIMP CONTACT:HR12-SC-212(CLI12-0408-9)
WIRE RANGE:AWG#26 TO 30(JACKET DIAMETER:φ1 MAX.)
APPLICABLE CRIMP CONTACT EXTRACTION TOOL:HR12-SC-TP(CLI150-0050-3)
- 2 APPLICABLE CRIMP TOOL, REF. NO. 7:HR10A-TC-02(CLI150-0041-2)
APPLY TO φ5.3.
- 3 THE RECOMMENDED CLAMP TORQUE, REF. NO. 5:1.5 TO 2N·m.
- 4 ACROSS FLATS HEXAGON HEAD OF REF. NO. 6:1.27.
THE RECOMMENDED CLAMP TORQUE, REF. NO. 6:0.3 TO 0.4N·m.
- 5 LOCTITE 242, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. 1, 6 FOR LOOSENING.
- 6 ONE EXAMPLE OF THE ROTATION OF REF. NO. 1 TO REF. NO. 5 IS SHOWN.
- 7 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE.
PLEASE CONFIRM BEFORE THE USE.

4	BRASS	MATTE FINISH NICKEL PLATED	8	CHLOROPRENE RUBBER	(BLACK)
3	POLYBUTYLENE TEREPHTHALATE	(BLACK) UL94V-0	7	BRASS	
2	STAINLESS STEEL		6	STEEL	NICKEL PLATING M2.6X0.45X2
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	5	BRASS	MATTE FINISH NICKEL PLATED
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS

UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
APPROVED :MO. SATOH 06.12.21				DRAWING NO. EDC4-021661-73			
CHECKED :EJ. KUNII 06.12.20				PART NO. HR10A-7J-4SC(73)			
DESIGNED :TO. HORII 06.12.19				CODE NO. CL110-0510-2-73			
DRAWN :MK. SATO 06.12.15							