


Dec.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES
- 1 APPLICABLE CRIMPING CONTACT
:HR10-PC-212(CL110-0514-3)
APPLICABLE WIRE:AWG#26~30
(COVERED WIRE MAX OUTSIDE DIA:Ø1)
APPLICABLE CONTACT EXTRACTION TOOL
:HR12-SC-TP(CL150-0039-0)
 - 2 HAND CRIMPING TOOL.REF.NO.⑦
:HR10A-TC-02(CL150-0041-2)
THE HOLE DIAMETER FOR CRIMPING:Ø5.3
 - 3 THE RECOMMENDED CLAMP TORQUE.
REF.NO.⑤: 1.5 TO 2N·m
 - 4 ACROSS FLATS HEXAGON HEAD OF REF.NO.⑥:1.27
THE RECOMMENDED CLAMP TORQUE.
REF.NO.⑥:0.3 TO 0.4N·m
 - 5 LOCTITE 263:HENKEL JAPAN OR EQUIVALENT APPLIES
TO PREVENT REF.NO.①AND ⑥FROM LOOSENING.
 - 6 ONE EXAMPLE OF THE ROTATION OF REF.NO.⑤TO
REF.NO.①IS SHOWN.
 - 7 THE ASSEMBLY THIS PRODUCT APPLIES TO
THE MANUAL ETAD-C0354-00.

4	STEEL	NICKEL PLATING	8	CHLOROPRENE RUBBER	(BLACK)
3	BRASS	MATTE FINISH NICKEL PLATED	7	BRASS	
2	POLYBUTYLENE TEREPHTHALATE	(BLACK) UL94V-0	6	STEEL	NICKEL PLATING
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	5	BRASS	NICKEL PLATING
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2 : 1	COUNT 2	DESCRIPTION OF REVISIONS DIS-C-00017346	DESIGNED HT. ZENBA	CHECKED HY. KOBAYASHI	DATE 20240508
APPROVED :MO. SATOH 20060530				DRAWING NO. EDC4-021662-73			
CHECKED :EJ. KUNII 20060529				PART NO. HR10A-7P-6PC(73)			
DESIGNED :DS. MATSUNE 20060526				CODE NO. CL0110-0503-7-73			
DRAWN :MK. SATO 20060525							