





NOTES

- 1 APPLICABLE CRIMPING TOOL OF REF. NO. ⑨: HR10A-TC-02 (CL150-0041-2)
THE HOLE DIAMETER FOR CRIMPING : Ø7.0
- 2 THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑦ : 2 TO 2.5 N · m.
- 3 ACROSS FLATS HEXAGON HEAD OF REF. NO. ⑧ : 1.27
THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑧ : 0.3 TO 0.4 N · m.
- 4 LOCTITE 243, HENKEL JAPAN OR EQUIVALENT IS
RECOMMENDED TO PREVENT REF. NO. ① AND ⑧ FROM LOOSENING.
- 5 ONE EXAMPLE OF THE ROTATION OF REF. NO. ⑦ TO REF. NO. ① IS SHOWN.
- 6 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS
MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE, PLEASE CONFIRM
BEFORE THE USE.

5	POLYAMIDE	(BLACK) UL94V-0	10	CHLOROPRENE RUBBER	(BLACK)
4	PHOSPHOR BRONZE	SILVER PLATING 2µm min.	9	BRASS	
3	PHOSPHOR BRONZE		8	STEEL	NICKEL PLATING HEXAGON SOCKET SET SCREW M2.6X0.45X3
2	STAINLESS STEEL		7	BRASS	MATTE FINISH NICKEL PLATED
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	6	BRASS	MATTE FINISH NICKEL PLATED
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS

UNITS
mm



SCALE
2 : 1

COUNT
△

DESCRIPTION OF REVISIONS

DESIGNED

CHECKED

DATE

HRS

HIROSE
ELECTRIC
CO., LTD.

APPROVED : EJ. KUNII

12. 11. 26

CHECKED : HY. KISHI

12. 11. 26

DESIGNED : HS. NAGANO

12. 11. 26

DRAWN : HS. NAGANO

12. 11. 26

DRAWING
NO.

EDC4-042722-73

PART
NO.

HR10G-10J-12S(73)

CODE
NO.

CL110-1619-7-73

△ 1/1