


Apr.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES
1. APPLICABLE CRIMP CONTACT: HR22-PC-222 (CL122-0009-0)
※APPLICABLE WIRE: AWG#24 TO 28, JACKET DIAMETER: $\phi 1.15$ (MAX)
APPLICABLE CONTACT REMOVAL TOOL (EXTRACTION TOOL): RP6-SC-TP (CL150-0039-0)
 - 2 THE RECOMMENDED CLAMP TORQUE, REF. NO. 5 : 2 TO 3 N · m.
AND LOCTITE 243, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO
PREVENT FROM LOOSENING.

3	Silicone rubber	(Black)							
2	Polybutylene terephthalate	(Black)	UL94V-0	5	Brass	Nickel plating			
1	Zinc alloy	Nickel plating		4	Brass	Nickel plating			
NO.	MATERIAL	FINISH	REMARKS	NO.	MATERIAL	FINISH	REMARKS		
UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS			DESIGNED	CHECKED	DATE
HIROSE ELECTRIC CO., LTD.			APPROVED	: EJ. KUNII	16.02.13	DRAWING NO.	EDC-042800-73-00		
			CHECKED	: EJ. KUNII	16.02.13	PART NO.	HR22-12WTRA-20PC(73)		
			DESIGNED	: SJ. SHIMIZU	16.02.13	CODE NO.	CL122-0005-0-73		
			DRAWN	: SJ. SHIMIZU	16.02.13				