








Apr.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




- Notes.
- 1 Co-planarity is within 0.1 mm.
 - 2 As for part No.4 the performance remains good though there might be a difference in the plating luster between each plating lots.
 - 3 Per reel : 450 pcs.
The vacuum cap(part No.5) is attached to this product at delivery.
 - 4 Refer to the mated condition diagram for the panel thickness and layout.
 - 5 This product is mounted by reflow soldering.
Refer to specification sheet ELC-129413-00-00 for reflow soldering.



3D image



				7	PET	△	
				6	PS		
				5	PA		Black, UL94V-0
				4	Stainless Steel		Surface : Tin 1μm min. Under plating : Nickel 0.2μm min.
3	Stainless Steel						
2	PA	Gray, UL94V-0					
1	Copper Alloy	Contact area : Gold 0.2μm min. Lead area : Gold 0.03μm min. Under plating : Nickel 2μm min.					
NO.	MATERIAL	FINISH	REMARKS	NO.	MATERIAL	FINISH	REMARKS
UNITS	mm	SCALE	5:1	COUNT	△	3	DESCRIPTION OF REVISIONS
						DIS-E-00011281	
						DESIGNED SN. TOYOSHIMA	
						CHECKED KI. KAGOTANI	
						DATE 2022. 10. 04	
						APPROVED : RI. TAKAYASU 2018. 04. 23	
						CHECKED : KI. NAGANUMA 2018. 04. 20	
						DESIGNED : YS. SAKODA 2018. 04. 20	
						DRAWN : YS. SAKODA 2018. 04. 20	
						DRAWING NO. EDC-129413-00-00	
						PART NO. IX80G-B-10P	
						CODE NO. CL0251-0019-0-00	
						△ 1 3	



Apr.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

