





	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					. .	△					. .
△						△					. .
△						△					. .



NOTES ① THE RECOMMENDED CLAMP TORQUE OF REF.NO. ①: 3 TO 3.5N · m
LOCTITE 271, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT
REF.NO. ① FROM LOSSENING.
② THE RECOMMENDED CLAMP TORQUE OF REF.NO. ④: 0.65 TO 0.7N · m

2	POLYPHENYLENE SULFIDE	(BLACK) UL94V-0	4	STAINLESS STEEL	M3×0.5×8
1	BRASS	BLACK CHROME PLATING	3	ACRYLONITRILE BUTADIENE RUBBER	(GLAY)
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

CODE NO. (OLD) CL	DRAWN <i>M. Sato</i> 06.12.27	DESIGNED <i>D. Matsume</i> 06.12.27	CHECKED <i>Y. Yamada</i> 06.12.27	APPROVED <i>M. Sato</i> 06.12.27	RELEASED
----------------------	-------------------------------------	---	---	--	----------

	DRAWING NO.	PART NO.
	EDC4-110462-71	JR16WCC-12(71)
SCALE 2 : 1	 HIROSE ELECTRIC CO.,LTD.	CODE NO.
UNITS mm		CL114-2056-7-71