


May.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES 1. APPLICABLE WIRE IS AWG #20~#22.(UL1007,UL1015)
INSULATION DIAMETER ϕ 2.70mm MAX.
2. APPLICABLE CRIMPING MACHINE AND CRIMPING CONDITIONS
(CRIMP HEIGHT etc.) WILL BE SPECIFIED ACCORDING TO
AWG # OR WIRE APPLIED.
3. ONE PACKAGE CONSISTS OF 100 PCS.
4. REFER TO ATAI-E3038 FOR CRIMP QUALITY STANDARDS.

				1	COPPER ALLOY		CONTACT AREA : GOLD PLATING 0.2μm MIN. TERMINAL AREA : TIN PLATING 1μm MIN. UNDER PLATING : NICKEL PLATING 0.5μm MIN.		
NO.	MATERIAL		FINISH , REMARKS		NO.	MATERIAL		FINISH , REMARKS	
UNITS mm		SCALE 5 : 1		COUNT 1	DESCRIPTION OF REVISIONS DIS-E-004910		DESIGNED TY. MIURA	CHECKED NM. NISHIMATSU	DATE 14. 01. 20
 HIROSE ELECTRIC CO. , LTD.			APPROVED : RI. TAKAYASU 12. 12. 11		DRAWING NO. EDC3-128192-00				
			CHECKED : AH. KODAMA 12. 12. 11		PART NO. PQ50-2022SCA				
			DESIGNED : TY. MIURA 12. 12. 10		CODE NO. CL236-2045-6-00				
			DRAWN : TY. MIURA 12. 12. 10		 1/1				