

Outdoor Rated Low PIM 7/16 DIN Male to N Female Cable SPO-375 Coax Using Times Microwave Parts

The 7/16 DIN male to type N female 60 inch cable using SPO-375 coax, part number FMCA2568-60, from Fairview Microwave is in-stock and ships same day. This Fairview 7/16 DIN to type N cable assembly has a male to female gender configuration with 50 ohm corrugated SPO-375 coax. Fairview Microwave's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. Our low PIM design offers excellent passive intermodulation performance with PIM levels better than -160 dBc. The FMCA2568-60 7/16 DIN male to type N female cable assembly operates to 6 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		83		%
Passive Intermodulation			-160	dBc
Capacitance		24 [78.74]		pF/ft [pF/m]

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2.5	4	6	GHz
Insertion Loss (Typ.)	0.3	0.42	0.67	0.85	1.07	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1*SQRT(FGHz) dB per connector.

Mechanical Specifications

Cable Assembly

Length*	60 in [152.4 cm]
Weight	0.288 lbs [130.63 g]

Cable

Cable Type	SPO-375
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Aluminum
Dielectric Type	Foam PE
Number of Shields	1
Outer Conductor Material and Plating	Copper



Configuration:

- 7/16 DIN Male
- N Female
- SPO-375

Features:

- Max Frequency 6 GHz
- Low PIM: -160 dBc Max
- 83% Phase Velocity
- PE Jacket
- 100% Tested with PIM Test Results Marked on Cable
- Lightweight and Extremely Flexible
- Low Loss with Excellent VSWR
- IP67 (when mated)
- Using Times Microwave Components

Applications:

- General Purpose
- Laboratory Use
- Low PIM Applications
- Outdoor Rated Applications
- Distributed Antenna Systems (DAS)
- Multi-Carrier Communication Systems
- PIM Testing

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Jacket Material PE, Black
 Jacket Diameter 0.43 in [10.92 mm]
 One Time Minimum Bend Radius 1.75 in [44.45 mm]

Connectors

Description	Connector 1	Connector 2
Type	7/16 DIN Male	N Female
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Brass, Silver	Brass, Silver
Contact Plating Spec.	200 µin	196 µin
Dielectric Type	PTFE	PTFE
Outer Cond Material & Plating		Brass, Tri-Metal
Outer Cond Plating Spec.		118 µin
Body Material & Plating	Brass, Tri-Metal	
Body Plating Spec.	100 µin	
Coupling Nut Material & Plating	Brass, Tri-Metal	Brass, Tri-Metal
Coupling Nut Plating Spec.	100 µin	118 µin
Torque		6 in-lbs 0.68 Nm

Environmental Specifications

Temperature

Operating Range -40 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FMCA2568 - xx uu

cm = Centimeters
 <blank> = Inches
 Length


Example: FMCA2568-12 = 12 inches long cable
 FMCA2568-100cm = 100 cm long cable

Outdoor Rated Low PIM 7/16 DIN Male to N Female Cable SPO-375 Coax Using Times Microwave Parts from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [Outdoor Rated Low PIM 7/16 DIN Male to N Female Cable SPO-375 Coax Using Times Microwave Parts FMCA2568-60](#)

URL: <https://www.fairviewmicrowave.com/outdoor-rated-low-pim-7-16-din-male-to-n-female-cable-spo-375-coax-using-times-microwave-parts-fmca2568-60-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



REVISIONS				
REV.	DESCRIPTION	DATE	APPROVED	
A	INITIAL RELEASE	9/21/2021	A. GANWANI	

LENGTH MEASURED FROM
CONTACT TO CONTACT

2X
HEAT SHRINK BOOT

SPO-375

www.FAIRVIEWMICROWAVE.com
FMCA2568
S/N: XXXXXXXXX
(SEE NOTE 1)

PIM LEVEL
-zzzdBc
S/N: XXXXXXXXX
(SEE NOTE 2)

CONTACT

N FEMALE

7/16 DIN MALE

NOTES:

- CABLES 84" AND UNDER HAVE 1 LABEL CENTERED. CABLES OVER 84" HAVE 2 LABELS, ONE AT EACH END 12.0" FROM THE END OF THE CONNECTOR.
- 6" FROM CABLE END 1 PLACE FOR ALL LENGTHS OF CABLE.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

Fairview Microwave an INFINIT[®] brand TITLE Outdoor Rated Low PIM 7/16 DIN Male to N Female Cable SPO-375 Coax Using Times Microwave Parts		UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS <table style="width: 100%; font-size: x-small;"> <tr> <th colspan="2">TOLERANCES:</th> <th>CABLE LENGTH (L) TOLERANCES:</th> </tr> <tr> <td style="vertical-align: top;"> $X = \pm 2$ [5.08] $XX = \pm .02$ [.51] $XXX = \pm .005$ [.13] </td> <td style="vertical-align: top;"> FRACTIONS $\pm 1/32$ ANGLES $\pm 1^\circ$ </td> <td style="vertical-align: top;"> $L \leq 12$ [305] = ± 1 [25] / -0 12 [305] < $L \leq 60$ [1524] = ± 2 [51] / -0 60 [1524] < $L \leq 120$ [3048] = ± 4 [102] / -0 120 [3048] < $L \leq 300$ [7620] = ± 6 [152] / -0 300 [7620] < L = $\pm 5\%L$ / -0 </td> </tr> </table> ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. <table style="width: 100%; font-size: x-small;"> <tr> <td>SIZE A</td> <td>CAGE CODE 3FKR5</td> <td>DRAWN BY K.DANG</td> <td>ITEM NO. FMCA2568</td> <td>REV A</td> </tr> </table>	TOLERANCES:		CABLE LENGTH (L) TOLERANCES:	$X = \pm 2$ [5.08] $XX = \pm .02$ [.51] $XXX = \pm .005$ [.13]	FRACTIONS $\pm 1/32$ ANGLES $\pm 1^\circ$	$L \leq 12$ [305] = ± 1 [25] / -0 12 [305] < $L \leq 60$ [1524] = ± 2 [51] / -0 60 [1524] < $L \leq 120$ [3048] = ± 4 [102] / -0 120 [3048] < $L \leq 300$ [7620] = ± 6 [152] / -0 300 [7620] < L = $\pm 5\%L$ / -0	SIZE A	CAGE CODE 3FKR5	DRAWN BY K.DANG	ITEM NO. FMCA2568	REV A
TOLERANCES:		CABLE LENGTH (L) TOLERANCES:											
$X = \pm 2$ [5.08] $XX = \pm .02$ [.51] $XXX = \pm .005$ [.13]	FRACTIONS $\pm 1/32$ ANGLES $\pm 1^\circ$	$L \leq 12$ [305] = ± 1 [25] / -0 12 [305] < $L \leq 60$ [1524] = ± 2 [51] / -0 60 [1524] < $L \leq 120$ [3048] = ± 4 [102] / -0 120 [3048] < $L \leq 300$ [7620] = ± 6 [152] / -0 300 [7620] < L = $\pm 5\%L$ / -0											
SIZE A	CAGE CODE 3FKR5	DRAWN BY K.DANG	ITEM NO. FMCA2568	REV A									

THIRD-ANGLE PROJECTION

THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.

SHEET 1 OF 1

SCALE N/A

T-Rev.D