





Note 1 The tightening torque of Ref. No. ⑤: 2 to 2.5 N · m.
Apply Loctite 243 HENKEL JAPAN or equivalent to the threaded portion (M14 × 0.75) of Ref. No. ① in order to prevent loosening.

3	Polyphenylene sulfide	(Black)	6	Phosphor bronze	Nickel plating					
2	Copper alloy	Silver plating 5μm min.	5	Brass	Nickel plating					
1	Zinc alloy	Matte finish nickel plated	4	Polyphenylene sulfide	(Black)					
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS				
UNITS mm				SCALE 2 : 1		COUNT 1	DESCRIPTION OF REVISIONS DIS-C-00016538	DESIGNED TY. SUZUKI	CHECKED HY. KOBAYASHI	DATE 20240201
 HIROSE ELECTRIC CO., LTD.				APPROVED : TP. KOMATSU		20230612	DRAWING NO. EDC-006792-81-00			
				CHECKED : HY. KOBAYASHI		20230612	PART NO. RM12BRD-7S(81)			
				DESIGNED : HT. ZENBA		20230609	CODE NO. CL0109-0619-1-81			
				DRAWN : KR. SUZUKI		20230607	 1			