




- Notes
- ② 1 Applicable crimp contact:
RP19-SC-222/CL113-0266-2 (Applicable cable size : AWG#24 to #28.
Cable jacket outer diameter shall be $\phi 1.15\text{mm}$ or less.)
 - ② 2 Applicable cable crimping tool : RP13A-TC-01/CL150-0070-0
 - ② 3 Extraction tool : RP6-SC-TP/CL150-0039-0
 - ② 4 The tightening torque of Ref No. ⑥ : 0.15 to 0.2 N·m.
To prevent loosening Ref No. ⑥, use LOCTITE 243, HENKEL JAPAN or equivalent.
 - 5 Shall be disassembled when delivered.
 - 6 The cable pull and twisting strength and other characteristics may differ,
depending on the cable structure. Please confirm before the use.

4	Brass			7	Polyvinylchloride (Black)	
3	Polycarbonate	(Black) UL94V-0		6	Brass	Black chromete treatment (Trivalent chromium) JIS B 1111 M2X0.4X4
2	Polycarbonate	(Black) UL94V-0		5	Steel	Nickel plating
1	Polycarbonate	(Black) UL94V-0				
NO.	MATERIAL	FINISH .	REMARKS	NO.	MATERIAL	FINISH .
UNITS mm		SCALE 2 : 1	COUNT ② 3	DESCRIPTION OF REVISIONS DIS-C-00009807	DESIGNED TY. SUZUKI	CHECKED HY. KOBAYASHI
HIROSE ELECTRIC CO., LTD.		APPROVED :MR. YOSHIDA	20050105	DRAWING NO.	EDC-022069-71-71	
		CHECKED :MO. SATOH	20050105	PART NO.	RP13A-12PD-20SC(71)	
		DESIGNED :YH. YAMADA	20050105	CODE NO.	CL0113-0214-9-71	
		DRAWN :YH. YAMADA	20050105		② 1/1	