




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

Connector System: **Wire-to-Board**

Number of Positions: **20**

Centerline (Pitch): **2 mm [.079 in]**

Number of Rows: **2**

Features

Product Type Features

PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Sealable	No
Connector Product Type	Housing Assembly

Configuration Features

Number of Positions	20
Number of Rows	2

Body Features

Primary Product Color	Black
-----------------------	-------

Mechanical Attachment

Mating Retention	With
------------------	------

Housing Features

Centerline (Pitch)	2 mm[.079 in]
--------------------	---------------

Dimensions



Row-to-Row Spacing	3.3 mm[.129 in]
--------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-D9934-A15A
Receptacle and Tab Housing: 2.0 mm pitch, 125V

Also in the Series

Dynamic 1000 Series

Connector Contacts(40)

Connector Hardware(3)

Insertion & Extraction Tools(2)

PCB Headers & Receptacles(171)

Power Contacts(9)

Rectangular Power Connectors(130)

Wire-to-Board Headers & Receptacles (171)

Customers Also Bought

TE Part #T2030032002-000
HEF-0.3(AWG26-22)

TE Part #T2111062201-000
HMN-006-F

TE Part #T2040021100-000
HMM-10.0

TE Part #T2040022060-000
HMF-6.0

TE Part #T2071064201-000
H6BP-T2-F DOCKING FRAME_FIXED

TE Part #1-2348455-6
DYNAMIC 1200D HDR ASSY H 12PX BLACK TIN

TE Part #1-2366515-4
DYNAMIC D1000 SLIM REC HSG 4P X KEY

TE Part #1-2366600-4
DYNAMIC D1000 SLIM TAB HSG 4P X KEY



Documents

Product Drawings

D1100 HDR ASSY H 20P XBLACK PRE-TIN

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2379284-0_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2379284-0_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2379284-0_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL

English

UL

English