



RF Load 50 Watts Medium Power To 6 GHz Precision SMA Female

Electrical Specifications*

Description	Min	Тур	Max	Units
Frequency Range	DC		6	GHz
Impedance			50	Ohms
VSWR			1.25:1	
Input Power			50	Watts

^{*} Values at 25°C, sea level

Mechanical Specifications

TemperatureOperating Range

Operating Range +100 to -55 deg C

Size

 Length
 0.96 in [24.38 mm]

 Width/Dia.
 1.38 in [35.05 mm]

 Height
 0.57 in [14.48 mm]

Connector

Type SMA Female

Body Material and Plating Stainless Steel, Passivated

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

document)

RoHS Compliant Yes

REACH Compliant 06/15/2015

Plotted and Other Data

Notes:

- Values at 25 °C, sea level
- Heat Sink Required for Proper Operation. Unit is cooled by conduction to heak sink.



Features:


- RF Load Design: Precision
- · Connector: SMA Female
- Connection Method: Standard
- Body Style: Straight

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

sales@fairviewmicrowave.com



Typical Performance Data



RF Load 50 Watts Medium Power To 6 GHz Precision SMA Female from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: RF Load 50 Watts Medium Power To 6 GHz Precision SMA Female FMTR1007

URL: http://www.fairviewmicrowave.com/rf-load-50-watts-6-ghz-precision-sma-female-fmtr1007-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







^{*} THESE DIMENSIONS AND TOLERANCES SUPERSEDE NOTE #1 ON TITLE BLOCK.

NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm]. CROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM TITLE DWG NO CAGE CODE FMTR1007 3FKR5 RF Load 50 Watts Medium Power To 6 GHz Precision SMA Female CAD FILE 093015 SHEET SCALE N/A SIZE A 5568

^{*} Heat Sink Required for Proper Operation, Unit is cooled by conduction to heat sink*