



Application Tooling > Hand Crimping Tools



Tool Grade: **Premium Crimp Tooling**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **MIL Spec, TE Product Specification (114-)**
TE Certification: **Cannot be Certified**
Power Technology Type: **Battery, Hydraulic, Manual**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - W Crimp
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Cannot be Certified
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1490747-1 HYP10 HEAVY DUTY 12T HEAD	 TE Part # 132074-2 TERM, SOLIS, RT, 2/0, M8(5/16)	 TE Part # 36916 TERMINAL, SOLIS R 1/0 5/16	 TE Part # 36922-1 TERM, SOLIS R 2/0 5/16 90DEG
 TE Part # 321872 TERMINAL, SOLIS R 2/0 7/16	 TE Part # 36946 SPLICE, SOLIS PARA 1/0	 TE Part # 36915 TERMINAL, SOLIS R 1/0 1/4	 TE Part # 36919-1 STRATO-THERM, HR 1/0 1/2 NIPL
 TE Part # 323179 TERMINAL SOLIS R HR 1/0 M6(1/4)	 TE Part # 36925 TERMINAL, SOLIS R 2/0 1/2	 TE Part # 36934 BODY SOLIS RING 4/0 1/2	 TE Part # 321877 TERMINAL, SOLIS R 3/0 1/2





TE Part # 322291
TERMINAL,SOLIS R 1/0 1/2



TE Part # 36948
SPLICE,SOLIS PARA 2/0



TE Part # 36951
SPLICE,SOLIS PARA 4/0



TE Part # 322225
TERMINAL,SOLIS R 2/0 3/4



TE Part # 321873-2
STRATO-THERM, HR 2/0 1/2 NIPL



TE Part # 322222
TERMINAL,SOLIS R 3/0 5/8




TE Part # 321873
BODY SOLIS RING 2/0 1/2



TE Part # 320266
TERMINAL,SOLIS R 3/0 5/16


Customers Also Bought



TE Part #36269
TERMINAL,SOLIS FLAG R 12-10 6



TE Part #322347
SPLICE,SOLIS PARA HT 16-14



TE Part #448816-3
AMPLIMITE,ASY,RCPT,109,NM,CS,3




TE Part #1490413-2
HYP10 SOLIS HD 8AWG NEST




TE Part #1490413-3
HYP10 SOLIS 4AWG NEST



TE Part #1490413-7
HYP10 SOLIS 3/0AWG NEST




TE Part #E61165-000
55/4322-22-2/6-6L-CS2582



TE Part #C86492-000
55/6002-30-CML3-9CS2528



TE Part #D51576-000
55/6001-30-2/6-9CS2528



TE Part #419588-000
55/2322-22-2/6-9CS2528

Documents



Datasheets & Catalog Pages

AT-Hydraulic Crimp Tooling Solutions-1654519

English

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English