




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **4 – 6.63 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Product Length	20.3 mm[.811 in]
Compatible Insulation Diameter Range	3.81 – 5.08 mm[.15 – .2 in]
Wire Size	4 – 6.63 mm ²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

Packaging Features

Packaging Quantity	250
Packaging Method	Loose Piece/Carton

Other

Line	Premier
------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 180441-2 110 FASTON,REC.,20-16 AWG,TPBR	 TE Part # 8-61765-1 FASTON,ADAPTER 250 HOUSING REC&TAB TPBR	 TE Part # 180250 HHHT FSTON/FF 375 POS LOC 250 6-2 ASSY	 TE Part # 61810-2 FASTON .250 (6.3 MM) RECEPTACLE TPBR
---	--	---	--

Also in the Series | FASTON 250

 Compression Connectors(4)	 Crimp Terminal Housings(115)	 Insertion & Extraction Tools(6)	 Insulation Boots & Sleeves(16)
 Magnet Wire Terminals(1)	 PCB Terminals(133)	 Quick Disconnects(420)	 Splices(4)

Customers Also Bought



TE Part #CS8930-000
RSTI-68SA1210

TE Part #HD34-24-31ST-072
REC, 31P, AL, T, THD ADPT, DRAIN, 16, S

TE Part #5068114005
CGPT-25.4/12.7-2-SP

TE Part #100570-2
250 FASTON, REC., 14-17AWG, TPBR

TE Part #2-160256-2
250 FASTON, REC., 17-14 AWG, TPBR

TE Part #179227-1
CRIMP TYPE II REC CONTACT

TE Part #292156-3
CT RELAY HDR ASSY FREE HANGING

TE Part #8-1879501-9
CRGH2512 5% 4K7 2W

TE Part #1879502-6
CRGH2512 5% 22K 2W

TE Part #2385398-1
CABLE ASSY, CPC TO METRIMATE

Documents

Product Drawings
250 FASTON, REC., 12-10 AWG, TPBR

- CAD Files
- 3D PDF
- 3D
- Customer View Model
- ENG_CVM_CVM_180367-2_H.2d_dxf.zip
- English
- Customer View Model
- ENG_CVM_CVM_180367-2_H.3d_igs.zip
- English
- Customer View Model
- ENG_CVM_CVM_180367-2_H.3d_stp.zip
- English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications
.110,.187 & 250 Series FASTON Terminals



English

[Product Specification](#)

English

[Agency Approvals](#)

[Agency Approval Document](#)

English