




Automotive Parts > Automotive Terminals > TIMER, RECEPTACLE AND TAB



Terminal Type: **Tab**

Wire Size: **22 – 17 AWG**

Mating Tab Width: **2.8 mm [.11 in]**

Interface Plating: **Gold (Au)**

[All TIMER, RECEPTACLE AND TAB \(280\)](#)

Features

Product Type Features

Receptacle Style	180°
Primary Locking Feature	Locking Lance
Sealable	Yes

Body Features

Terminal Seal Type	Single Wire Seal (SWS)
--------------------	------------------------

Contact Features

Typical Current Rating	5 A
Crimp Type	F-Crimp
Contact Size	2.8mm
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Terminal Type	Tab
Mating Tab Width	2.8 mm[.11 in]
Interface Plating	Gold (Au)
Mating Tab Thickness	.8 mm[.031 in]

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------



Product Terminates To

Wire

Dimensions

Compatible Insulation Diameter Range	3.4 mm[.134 in]
Wire Size	22 – 17 AWG
Wire Size Search	.35 mm², .4 mm², .5 mm², .6 mm², .8 mm², 1 mm²
Tab Length	26.8 mm[1.05 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Packaging Features

Packaging Method	Reel
Packaging Quantity	3500

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 106462-1
2P.FASTIN-ON HSG.



TE Part # 7-2266458-7
OCEAN_2.0_SPARE_PART_KIT-070F155O



TE Part # 185001-6
4P TAB JPT HOUSING



TE Part # 2266458-1
OCEAN_2.0_APPLICATOR-S-070F155O-RSM



TE Part # 2266458-2
OCEAN_2.0_APPLICATOR-S-070F155O-RSA




TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No Crimp

Also in the Series | Junior Power Timer



Automotive Connector Caps & Covers (12)



Automotive Connector Locks & Position Assurance(8)



Automotive Housings(279)



Automotive Seals & Cavity Plugs(8)



Automotive Signal & Power Connector Housings(275)




Automotive Terminals(150)




Special Purpose Terminals(2)

Customers Also Bought



TE Part #5641733001
99M0111-26-0



TE Part #106462-1
2P.FASTIN-ON HSG.




TE Part #184139-1
WIRE SEAL,RUBBER,SENSOR,BLUE



TE Part #282190-1
SPLASH PROOF CONN. W.S.L.



TE Part #CAT-R7602-T273
ROUND CONNECTOR SYSTEM, PIN AND SOCKET




TE Part #963900-1
TAB A 1.6x0.6 CONTACT CS SRC Sn



TE Part #965785-1
ABDECKKAPPE 180GRD



TE Part #7-968973-1
AMP MCP 2.8 HSG 15 POS. 2. LOCKING



TE Part #1379681-1
24W TAB HSG ASSY BLACK

Documents

Product Drawings

TAB F 2.8x0.8 CONTACT CS SWS Sn

French

CAD Files

Customer View Model

ENG_CVM_185028-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_185028-1_A.3d_stp.zip

English

Customer View Model

ENG_CVM_185028-1_A.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



LANGUETTE JPT 2.8 X 0.8

English

LANGUETTE JPT 2.8 X 0.8

English

CLIP JUNIOR POWER TIMER POUR JOINT INDIVIDUEL

French