

Nextreme™ Performance Chiller


The Nextreme NRC1200 Recirculating Chiller Recirculating Chiller features premium components and environmentally friendly refrigerants in a user-friendly design. It is designed to cool well below ambient and dissipate heat away from thermally sensitive equipment. Featuring variable speed motors for the compressor and condensing fan, the Nextreme NRC1200 offers a high coefficient of performance and low-noise operation. The Nextreme NRC1200 comes with several standard features and additional options allow for application-specific configurations. Power cord is **not** supplied with the unit and **must be ordered separately**.

**Features**

- Reliable Performance
- Environmentally Friendly
- User-Friendly
- Application Specific Configurations

Applications

- Industrial Lasers
- Additive Manufacturing
- Electron Microscopes
- Semiconductor Fabrication
- Laboratory Testing

**Cooling Power Operating Points****100% Water (20°C Ambient Air)**

Cooling Power (Qc) = 1,400 Watts
Fluid Setpoint = 20 °C
Fluid ΔT @ 15.0 L/min = 1.4 °C

100% Water (30°C Ambient Air)



Cooling Power (Qc) = 900 Watts
Fluid Setpoint = 20 °C
Fluid ΔT @ 15.0 L/min = 0.9 °C

60/40 Water-Glycol (20°C Ambient Air)


Cooling Power (Qc) = 1,350 Watts
Fluid Setpoint = 20 °C
Fluid ΔT @ 15.0 L/min = 1.4 °C

60/40 Water-Glycol (30°C Ambient Air)

Cooling Power (Qc) = 850 Watts
Fluid Setpoint = 20 °C
Fluid ΔT @ 15.0 L/min = 0.9 °C

NRC1200-A1-20-ST1 Cooling Capacity
15 L/min Fluid FlowNRC1200-A1-20-ST1 ΔT (Inlet-Outlet) Fluid Temperature
Max System Cooling at 20°C Ambient Air
15 L/min Fluid Flow

NRC1200-A1-20-ST1 - Pump Curve



Technical Specifications

Performance

| | |
|---|----------------------|
| Nominal Cooling Capacity¹ | 1,400 W |
| Setpoint Range | -10°C to 40°C |
| Temperature Stability³ | ±0.10°C |
| Nominal Operating Flowrate (60 Hz)¹ | 15.0 L/min @ 2.6 Bar |
| Nominal Operating Flowrate (50 Hz)¹ | 15.0 L/min @ 1.5 Bar |
| Refrigerant (Fluorinated greenhouse gas) | R513A; GWP 631 |
| Refrigerant Charge | 350g |
| Sound Pressure Level at Nominal Cooling Capacity (50 Hz)¹ | 61 dBA |
| Sound Pressure Level at Nominal Cooling Capacity (60 Hz)¹ | 63 dBA |

Operation

| | |
|--|--|
| Coolant | Water or Water/Glycol |
| Operating Temperature² | 15°C to 40°C |
| Storage temperature range (w/o coolant) | -25°C to 70°C |
| Humidity range | 30% to 80% |
| Storage Humidity range | 5% to 95%, non-condensing |
| Altitude | < 2,000 meters |
| Input Voltage | 220 - 240 VAC |
| Frequency | 50 / 60 Hz |
| Current | < 8.1 Amps |
| Input Power Connection | C19 Receptacle |
| Maximum Forward Pressure | 4.1 Bar |
| Compliance | ANSI / UL / CSA / IEC EN 61010-1 Edition 3 |

Physical

| | |
|-------------------------|------------|
| Height | 670 mm |
| Length | 520 mm |
| Width | 450 mm |
| Weight | 48 kg |
| Coolant Capacity | 5 Liters |
| Couplings | 1/2 in NPT |

Standard Features

| | |
|-----------------------------------|--|
| Variable Speed Motors | Variable speed compressor and condensing fans for quiet operation and improved energy efficiency. |
| Semi-Closed Fluid System | Sealed fluid system with breathable reservoir cap (similar to an automobile). This prevents evaporative loses, introduction of bacteria, and the need for components to prevent fluid from draining back into the system when installed below the application. |
| Optical Fluid Level Switch | Fluid level sensing with no moving parts. |
| RS-232 Communications | Complete control integration of chiller into higher level assembly control system. |
| Supply Pressure Sensing | Pressure sensing for applications sensitive to high operating conditions. |

Accessory Kits

| | Feature | Kit Part Number | Description |
|---|---|------------------------|--|
|  | Flow Control Valve and Flow Sensing Kit | 387004277 | This externally installed valve is for reducing the overall flow to the application. Full flow continues through the chiller to maintain high heat transfer rates and temperature stability. The flow meter is for measuring coolant flow rate and is installed externally to the chiller with both a local display (GPM) and connectivity to the chiller LCD display. The flow rate local display is only on NRC products. This kit is for all refrigerant chillers: EFC2400, NRC1200, NRC2400, NRC5000, VRC1200, VRC2400, and VRC4500. |
|  | Water Filter Kit | 387004279 | Hot swappable, 5-micron water filter for filtering particulates from the coolant circuit. |
|  | Flow Bypass Kit | 387010608 | This externally installed valve is for reducing the overall flow to the application. Full flow continues through the chiller to maintain high heat transfer rates and temperature stability. |
|  | Pressure Bypass Kit | 387010420 | This pressure bypass kit prevents high pressure operation and can either operate partially open or open when there is a change in operation (e.g., flow to application stopped). It can be used for flow control but operates with less precision. This pressure bypass maintains full flow through the chiller heat exchanger. |


Cord Options

These power cords have been tested and validated on Nextreme devices.

Power cord is not supplied with the unit and must be ordered separately.

| MFG Part Number | Plug Type | Standard | Style | Cable Length | Rating | Color | Connector |
|-----------------|-----------|----------|--------------|--------------|----------------------|-------|-----------|
| 387005324 | Universal | None | Flying Leads | 2.0 m | 250VAC, 16A* / 20A** | Black | C19 |

* IEC ** UL



Notes

1. Nominal capacity rating is given at a 20°C (68°F) setpoint, 20°C (68°F) ambient temperature, sea level.
2. For ambient conditions outside this range, please contact Laird Thermal Systems.
3. Typical for nominal capacity rating. Contact LTS applications engineering for application specific performance.

Any information furnished by Tark Thermal Solutions and its agents, whether in specifications, data sheets, product catalogues or otherwise, is believed to be (but is not warranted as being) accurate and reliable, is provided for information only and does not form part of any contract with Tark Thermal Solutions. All specifications are subject to change without notice. Tark Thermal Solutions assumes no responsibility and disclaims all liability for losses or damages resulting from use of or reliance on this information. All Tark products are sold subject to the Tark Thermal Solutions Terms and Conditions of sale (including Tark's limited warranty) in effect from time to time, a copy of which will be furnished upon request.

© Copyright 2025 Tark Thermal Solutions, Inc. All rights reserved.

Nextreme™ is a trademark of Tark Thermal Solutions, Inc. All other marks are owned by their respective owners.

Revision: 08 Date: 12-07-2025

Print Date: 12-08-2025