

TSAS-NR501-X-25MM

✓ ACTIVE

RAYCHEM | RAYCHEM TSAS


TE Internal #: 5670416002

Clear, Single Wall, Adhesive, 2.3 mm [.091 in] Expanded Inside, Non-Flame-Retardant, Reel, -30 – 125 °C [-22 – 257 °F], Flexible, Global, RAYCHEM TSAS

[View on TE.com >](#)



Heat Shrink Tubing > SAS Heat Shrink Tubing



Primary Product Color: **Clear**

Wall Type: **Single Wall**

Expanded Inside Diameter (Min): **2.3 mm [.091 in]**

Primary Product Material: **Adhesive**

Tubing Flammability Type: **Non-Flame-Retardant**

[All SAS Heat Shrink Tubing \(34\)](#)

Features

Product Type Features

Wall Type	Single Wall
-----------	-------------

Body Features

Primary Product Color	Clear
Primary Product Material	Adhesive
Flexibility	Flexible

Dimensions

Product Length	25 mm[.984 in]
Expanded Inside Diameter (Min)	2.3 mm[.091 in]

Usage Conditions

Tubing Flammability Type	Non-Flame-Retardant
Operating Temperature Range	-30 – 125 °C[-22 – 257 °F]

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Reel
------------------	------



Other

Product Source	Czech Republic
----------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # EG1114-000
[CV1981-ST-230V1600W-EU](#)

Also in the Series | RAYCHEM TSAS



Heat Shrink Tubing(16)



Single Wall Tubing(16)

Customers Also Bought



TE Part #CAT-HST-QS1500
QS1500 Heat Shrink Tubing



TE Part #EM4884-000
VERSAFIT-3/8-2-25MM



TE Part #DT04-2P-CE03
REC, 2P, BLK, E, CAP




TE Part #CAT-HST-SCT
SCT Heat Shrink Tubing



TE Part #EL7577-000
CBS-18C902XUU3A-0



TE Part #220781P003
QS1500-NO.5-M1-0-75MM



TE Part #1-174985-1
E-J MK-2 CAP HSG 8P NATURAL

Documents

Product Drawings

TSAS-NR501-X-25MM

English

Datasheets & Catalog Pages

Selecting_Correct_Tubing_1216

English

Measuring_Single_Wall_Tubing

English

Product Specifications

Application Specification for General Purpose Dual Wall Heat Shrink Tubing Products

English