

TSAS-NR501-X-10MM

✓ ACTIVE

RAYCHEM | RAYCHEM TSAS

TE Internal #: 5670416008

Clear, Single Wall, Adhesive, 2.3 mm [.091 in] Expanded Inside, Non-Flame-Retardant, Box, -30 – 125 °C [-22 – 257 °F], Flexible, Global, RAYCHEM TSAS

[View on TE.com >](#)



Heat Shrink Tubing > SAS Heat Shrink Tubing



Primary Product Color: **Clear**

Wall Type: **Single Wall**

Expanded Inside Diameter (Min): **2.3 mm [.091 in]**

Primary Product Material: **Adhesive**

Tubing Flammability Type: **Non-Flame-Retardant**

[All SAS Heat Shrink Tubing \(34\)](#)

Features

Product Type Features

Wall Type	Single Wall
-----------	-------------

Body Features

Primary Product Color	Clear
Primary Product Material	Adhesive
Flexibility	Flexible

Dimensions

Product Length	10 mm[.393 in]
Expanded Inside Diameter (Min)	2.3 mm[.091 in]

Usage Conditions

Tubing Flammability Type	Non-Flame-Retardant
Operating Temperature Range	-30 – 125 °C[-22 – 257 °F]

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Box
------------------	-----



Other

Product Source	Czech Republic
----------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | RAYCHEM TSAS




Heat Shrink Tubing(16)




Single Wall Tubing(16)


Customers Also Bought



TE Part #170063-2
CLUSTER PIN REC



TE Part #171370-5
CLUSTER BLOCK HSG PBT



TE Part #175164-1
250 PL EX REC. 18-14AWG ST



TE Part #177901-1
POWER DBL LOCK PLUG HSG 6P



TE Part #177919-1
POWER DBL LOCK PLATE 3P



TE Part #179466-1
AMP POWER DBL LOCK CAP HSG 6P



TE Part #1-353047-2
DYNAMIC D-5200S TAB HSG 2P K/X



TE Part #9-965382-2
8POS MQS REC COD Z



TE Part #965383-1
MQS SICHERGSCHIEBER 8POS



TE Part #1612335-1
GRACE INERTIA 3.5 TAB CONTACT (M)

Documents

Product Drawings
TSAS-NR501-X-10MM

English

Datasheets & Catalog Pages
Selecting_Correct_Tubing_1216

English

Application Tooling for Raychem Heat Shrink Product

English



Measuring_Single_Wall_Tubing

English

Product Specifications

Quality Specification

English