


ALCOSWITCH

TE Internal #: 6-1437622-8

Aluminum, Straight Knurl Knob Design, 6.35 mm [.25 in] Shaft, 24.1 mm [.949 in] Diameter, Black, Line Indicator, Switch Knobs

[View on TE.com >](#)

Switches > Switch Knobs



Primary Product Material: Aluminum

Knob Design: Straight Knurl

Shaft Size: 6.35 mm [.25 in]

Product Diameter: 24.1 mm [.949 in]

Primary Product Color: Black

Features

Configuration Features

Spinner	Without
Skirt	Without
Spin Plate	Without
Knob Design	Straight Knurl

Body Features

Primary Product Material	Aluminum
Primary Product Color	Black

Dimensions

Shaft Size	6.35 mm [.25 in]
Product Diameter	24.1 mm [.949 in]

Identification Marking

Indicator Style	Line
Indicator Location	Side

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought

TE Part #306354-000
44AM1131-22-9/93/96-9TE Part #TRA7603
OMNI, Ph, NMO, 760-870MHZ WHT,
3,100,TE Part #1-292207-0
MINI CT SGL DIP V 10P NATTE Part #1-353293-0
MINI CT MT REC ASSY 10P GRAYTE Part #2-1437558-0
MTA206N=(MSTA) SW TOG DPDTTE Part #2-1437558-2
MTA206P=(MSTA) SW TOG DPDTTE Part #2-1437622-7
KN1250B1/4=KNOB BLACK KNURL 1/TE Part #2267074-4
PMS9P1B05M2QETE Part #071275-000
RNF-100-1/2-BK-FSPTE Part #6-2176093-4
RP 2A 0.25W 46K4 0.1% 25PPM 1K RL

Documents

CAD Files

[3D PDF](#)
[3D](#)

Customer View Model

[ENG_CVM_CVM_6-1437622-8_99_c-6-1437622-8-99.2d_dxf.zip](#)
[English](#)

Customer View Model

[ENG_CVM_CVM_6-1437622-8_99_c-6-1437622-8-99.3d_igs.zip](#)
[English](#)

Customer View Model

[ENG_CVM_CVM_6-1437622-8_99_c-6-1437622-8-99.3d_stp.zip](#)
[English](#)

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.