




Automotive Parts > Automotive Connector Accessories > Automotive Connector Locks & Position Assurance > Wedgelocks: DEUTSCH DT



Number of Positions: 2

Primary Product Color: Orange

Connector & Contact Retention Accessory Type: Secondary Lock

Primary Product Material: PBT

Operating Temperature Range: -55 – 125 °C [-67 – 257 °F]

[All Wedgelocks: DEUTSCH DT \(58\)](#)

Features

Product Type Features

Sealable	No
Connector & Contact Retention Accessory Type	Secondary Lock

Configuration Features

Number of Positions	2
---------------------	---

Body Features

Primary Product Color	Orange
Primary Product Material	PBT

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

--	--



Packaging Method	Box
Other	
Serviceable	Yes

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # YDT06-2S-W2S-CONTS DT06-2S WEDGE & CONTACTS	 TE Part # CAT-J41-DDCC DEUTSCH DT Color Connectors	TE Part # DT06-2S-CE02 PLG, 2P, BLK, E	TE Part # YDT06-2S-E008W2SKT DT06-2S-E008 WITH W2S
--	---	---	---



TE Part # DT-RT1
EXT TOOL, FRONT RELEASE

TE Part # CAT-J41-DDPC
DEUTSCH DT Plug Connectors

TE Part # CAT-D487-W416
Wedgelocks: DEUTSCH DT

Also in the Series

DEUTSCH DT

Automotive Connector Caps & Covers
(19)

Circular Connector Backshells &
Clamps(2)

Rectangular Connector Housings(1)

Wire-to-Board Connector Assemblies
& Housings(1)

Customers Also Bought

TE Part #HC5730
LEAD CONNECTOR 25MM +VE

TE Part #HC5841
70MM2 BATTERY CLMP ASSMB
NEGATIVE

TE Part #DTV02-18PA-C015
REC, 18P, GRY, E, FLANGE, A

TE Part #HC5728
LEAD CONNECTOR 16MM

TE Part #HC5732
LEAD CONNECTOR 35mm +VE

TE Part #HC5936
BATTERY LEAD CONN. 70mm +VE

TE Part #282191-1
SPLASH PROOF CONN. W.S.L.

TE Part #429605-ZZ
SQ.HEAD BOLT 5/16 UNC x 1-
ELECTRO TI

TE Part #429604-ZZ
5/16 UNC HEXAGON NUT ELECTRO
TIN P

TE Part #1625990-2
R1339 16R 5%



Documents

Product Drawings

SEAL RETN WEDGE. ORANGE DT 2 W

English

CAD Files

Customer View Model

ENG_CVM_CVM_W2S-P070-Y_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_W2S-P070-Y_A.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_W2S-P070-Y_A.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English