



Image for illustrative purpose only

Summary

[Request a quote](#)

[P series catalog](#)

[Customer Drawing](#)

| | |
|------------------------------------|----------------------------|
| Number of contacts Low Voltage | 19 |
| Wire Size/AWG | 30 - 22 |
| Gender | Standard |
| Socket / Receptacle | Socket / Receptacle - Free |
| Locking system | Push-pull |
| Jacket cable outside diameter [mm] | 7.30 - 9.20 mm |
| Size | 2P |
| Series | REDEL P - Push-Pull |

Technical details

Electrical Configuration

| | |
|------------------------------------|-----------------------------|
| Number of contacts Low Voltage | 19 |
| Contact Termination Low voltage | Solder |
| Insert configuration value | 2P.M19 - 19 Low V. |
| Footprint IPC Class3 compatibility | No |
| Insulator | L: PEEK for solder contacts |
| Rated current | 4.5 A |
| Test voltage contact-contact | 1.48 (kV DC) |
| Air clearance | 0.6 mm |
| Creepage distance | 0.6 mm |
| Bucket Dia. | 0.8 mm (0.031in) |
| Contact Dia. | 0.7 mm (0.027in) |
| Wire Size/AWG | 30 - 22 |
| Gender | Standard |

Form & Material

| | |
|------------------------|---|
| Shell style / Model id | CR - Free receptacle with cable collet |
| Socket / Receptacle | Free |
| Housing material | PSU (Polysulfone), grey |
| Locking system | Push-pull |
| Keying | B: 3 keys (alpha=0, gamma=60, Plug: male contacts, Receptacle: female contacts) |
| Colour | Grey |
| Weight | 11.84 g |

Environment

| | |
|-----------------------------------|--|
| Technical domain | Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV |
| Environmental sealing (IP rating) | IP50 |
| Endurance | >1000 mating cycles |
| Temperature range | -50°C / +150°C |
| F ret (max) | 250 N |
| F ret (min) | 150 N |
| Steam sterilization | Compiles with ISO 17665:2024 sterilization standard for autoclave, ISO 11135:2014 for EtO, and ISO 11137-1, -2, -3 standards for gamma, e-beam x-ray. For more details on sterilization methods and cycles, please contact us. |

Cable fixation

| | |
|------------------------------------|--|
| Cable termination protection | Standard back nut (no additional protection) |
| Fixation type | Cable collet |
| Jacket cable outside diameter [mm] | 7.30 - 9.20 mm |

https://www.lemo.com/int_en/solutions/rede/rede-p-push-pull/crb-m19-gll-c92g.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.