


REVISIONS									
P	LTR	DESCRIPTION						DATE	APVD
	H1	REVISED AS PER ECR-25-244807						19MAY2025	JM


8.7	GEN II & GEN III	 PA9T	2.30	71.35	70	73.15	89	71.65	164	BLACK	30u"	4-1734774-8
5.45				38.35	37	40.15	56	38.65	98	WHITE		4-1734774-7
										BLACK		4-1734774-6
3.85				21.35	20	23.15	39	21.65	64	WHITE		4-1734774-5
										BLACK		4-1734774-4
2.55				7.35	6	9.15	25	7.65	36	WHITE		4-1734774-3
										BLACK	4-1734774-2	
8.7				71.35	70	73.15	89	71.65	164	BLACK	15u"	4-1734774-0
										G/F	3-1734774-9	
										WHITE	15u"	3-1734774-8
											G/F	3-1734774-7
5.45				38.35	37	40.15	56	38.65	98	BLACK	15u"	3-1734774-6
										G/F	3-1734774-5	
										WHITE	15u"	3-1734774-4
											G/F	3-1734774-3
3.85				21.35	20	23.15	39	21.65	64	BLACK	15u"	3-1734774-2
										G/F	3-1734774-1	
										WHITE	15u"	3-1734774-0
											G/F	2-1734774-9
2.55				7.35	6	9.15	25	7.65	36	BLACK	15u"	2-1734774-8
	G/F	2-1734774-7										
	WHITE	15u"	2-1734774-6									
		G/F	2-1734774-5									
8.7	GEN II & GEN III	 PA9T	3.10	71.35	70	73.15	89	71.65	164	BLACK	30u"	2-1734774-4
5.45				38.35	37	40.15	56	38.65	98	WHITE		2-1734774-3
										BLACK		2-1734774-2
3.85				21.35	20	23.15	39	21.65	64	WHITE		2-1734774-1
										BLACK		2-1734774-0
2.55				7.35	6	9.15	25	7.65	36	WHITE		1-1734774-9
										BLACK	1-1734774-8	
8.7				71.35	70	73.15	89	71.65	164	WHITE	15u"	1-1734774-7
										BLACK	15u"	1-1734774-6
											G/F	1-1734774-5
										WHITE	15u"	1-1734774-4
G/F				1-1734774-3								
5.45				38.35	37	40.15	56	38.65	98	BLACK	15u"	1-1734774-2
										G/F	1-1734774-1	
										WHITE	15u"	1-1734774-0
											G/F	1734774-9
3.85				21.35	20	23.15	39	21.65	64	BLACK	15u"	1734774-8
										G/F	1734774-7	
										WHITE	15u"	1734774-6
											G/F	1734774-5
2.55	7.35	6	9.15	25	7.65	36	BLACK	15u"	1734774-4			
							G/F	1734774-3				
							WHITE	15u"	1734774-2			
								G/F	1734774-1			
WEIGHT(g)	PCI-E COMPLIANCE	HOUSING MATERIAL	DIM. L	DIM. E	DIM. D	DIM. C	DIM. B	DIM. A	POS.	HOUSING COLOR	MIN. GOLD THICKNESS	PART NUMBER

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—




PN X-1 TO 4-X-8
(PA9T TYPE)



36 POS.





PN 5-X-0 TO 9-X-8
(PA46 TYPE)




64 POS.




98 POS.




164 POS.




PRELIMINARY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TONY LI 21SEP2022		TE Connectivity Ltd.		
		CHK HOPE LU 21SEP2022				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PCI EXPRESS CARD EDGE CONNECTOR VERTICAL DIP TYPE, GEN3 —		
		APVD HOPE LU 21SEP2022				
0 PLC ± — 1 PLC ± 0.30 2 PLC ± 0.20 3 PLC ± 0.15 4 PLC ± — ANGLES ± 3°		PRODUCT SPEC 108-57871		SIZE A3		
		APPLICATION SPEC —				
		MATERIAL —		WEIGHT 0		CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO C-1734774		
				RESTRICTED TO —		
				SCALE 1:1		
				SHEET 3 of 6		
				REV H1		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




TOLERANCE: ± 0.05
FOR DIM.L=3.1mm PCB THICKNESS: 2.4mm
FOR DIM.L=2.3mm PCB THICKNESS: 1.6mm



TOLERANCE: ± 0.05
FOR DIM.L=3.1mm PCB THICKNESS: 2.4mm
FOR DIM.L=2.3mm PCB THICKNESS: 1.6mm






ADD-IN CARD EDGE-FINGER DIMENSIONS

NOTES:
CHAMFER EDGE MUST BE FREE OF CUTTING BURRS




164	70.0	73.15	72.15	A1, B17, B31, B48, B81
98	37.0	40.15	39.15	A1, B17, B31, B48
64	20.0	23.15	22.15	A1, B17, B31
36	6.0	9.15	8.15	A1, B17
POS.	DIM. F	DIM. G	DIM. H	"K"

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TONY LI 21SEP2022	 TE Connectivity Ltd.		
		CHK HOPE LU 21SEP2022			
		APVD HOPE LU 21SEP2022	NAME PCI EXPRESS CARD EDGE CONNECTOR VERTICAL DIP TYPE, GEN3		
DIMENSIONS: mm		PRODUCT SPEC 108-57871			
		APPLICATION SPEC			
		WEIGHT 0	SIZE A3	CAGE CODE 00779	DRAWING NO C-1734774
		CUSTOMER DRAWING	SCALE 1:1	SHEET 4 OF 6	REV H1




4. WEIGHT : SEE TABLE



10.2 Kg	8.2 Kg	30	10	3	900	164
9.0 Kg	7.0 Kg	40	10	3	1200	98
8.5 Kg	6.5 Kg	60	10	3	1800	64
7.6 Kg	5.6 Kg	70	10	3	2100	36
GROSS WEIGHT	NET WEIGHT	PCS/TRAY	TRAY/CARTON	CARTON/BOX	PCS/BOX	POS.


2. ALL OTHER PN USE PACKAGING 1 SHEET 5

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TONY LI 21SEP2022		TE Connectivity Ltd.				
DIMENSIONS: mm 		CHK HOPE LU 21SEP2022						
		APVD HOPE LU 21SEP2022		NAME PCI EXPRESS CARD EDGE CONNECTOR VERTICAL DIP TYPE, GEN3 —				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± 0.30 2 PLC ± 0.20 3 PLC ± 0.15 4 PLC ± — ANGLES ± 3°		PRODUCT SPEC 108-57871						
		APPLICATION SPEC —						
		WEIGHT 0						
MATERIAL —		FINISH —		SIZE	CAGE CODE	DRAWING NO	RESTRICTED	
				A3	00779	©-1734774	—	
CUSTOMER DRAWING						SCALE	SHEET	REV
						1:1	5 OF 6	H1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

- NOTES :
- 1. MATERIAL :
TRAY : PVC, COLOR: TRANSPARENT.
BOX: CORRUGATED FIBER
 - 2. DIMENSION :
TRAY: SEE DRAWING
BOX : SEE DRAWING
 - 3. QUANTITY : SEE TABLE
 - 4. WEIGHT : SEE TABLE

4.4 Kg	2.4 Kg	60	10	600	64	9-1734774-8
GROSS WEIGHT	NET WEIGHT	PCS/ TRAY	TRAY/ CARTON	PCS/ BOX	POS.	TCPN



PACKAGING 2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TONY LI	21SEP2022	TE Connectivity Ltd.		
		CHK HOPE LU	21SEP2022			
		APVD HOPE LU	21SEP2022	NAME PCI EXPRESS CARD EDGE CONNECTOR VERTICAL DIP TYPE, GEN3		
		PRODUCT SPEC 108-57871				
		APPLICATION SPEC				
		WEIGHT	0	SIZE	CAGE CODE	DRAWING NO
		CUSTOMER DRAWING		A3	00779	C-1734774
				SCALE	1:1	SHEET 6 OF 6
				REV		H1